

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Flush-type connector, Power, 5-position, Socket, straight, L - Power, PCB mounting, THR solder connection

Your advantages

- For compact devices: transmit high power in a confined space
- ☑ Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- ✓ All common pin assignments and codings available
- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Additional gasket for the device when not plugged in



Key Commercial Data

Packing unit	60 pc
Minimum order quantity	60 pc
GTIN	4 055626 427287
GTIN	4055626427287
Weight per Piece (excluding packing)	5.180 g
Custom tariff number	85366990
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Ambient conditions

Ambient temperature (operation)	-25 °C 105 °C	
	-40 °C 105 °C (without mechanical actuation)	
Degree of protection	IP67 (correctly plugged in and locked)	

General



Technical data

General

Note	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
	FE not connected to metal parts that can be touched, no protective function
Rated current at 40°C	16 A
Rated voltage	63 V
Rated surge voltage	1.5 kV
Number of positions	5
Coding	L - Power
Standards/regulations	M12 connector IEC 61076-2-111 In line with
Signal type/category	Power
Overvoltage category	III
Degree of pollution	3
Connection method	THR solder connection
Insertion/withdrawal cycles	> 100
Mounting type	PCB mounting
Type of packaging	Tray
Delivery state	with assembly pad

Material

Flammability rating according to UL 94	V0
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA4T
Sealing material	FKM

Cable

Standards/specifications	M12 connector IEC 61076-2-111 In line with

Standards and Regulations

Standard designation	M12 connector
Standards/regulations	IEC 61076-2-111
Flammability rating according to UL 94	V0

Environmental Product Compliance

REACh SVHC	Lead 7439-92-1	
China RoHS	Environmentally Friendly Use Period = 50	
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"	

Drawings



Dimensional drawing




Dimensional drawings can be found under Downloads

Schematic diagram




Pin assignment of M12 socket, 5-pos., L-coded, socket side view

Drilling diagram



Soldering pad geometry

Dimensional drawing



THR tray packaging

Classifications

eCl@ss

eCl@ss 4.0	27140815
	27 140813
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27440103
eCl@ss 9.0	27440103

ETIM

ETIM 6.0	EC002061

Approvals

Approvals



Approvals		
Approvals		
cULus Recognized		
Ex Approvals		

Approval details

cULus Recognized	c 711 us	http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm E468743-2018011	
Nominal voltage UN			63 V
Nominal current IN			16 A

Phoenix Contact 2019 @ - all rights reserved http://www.phoenixcontact.com