

TECHNICAL DATA SHEET

Carbon steel type C

General notes:

- Carbon style (material number 1.1221, Ck60, AISI 1060)
- contains from 0,57-0,65 wt% carbon
- magnetizable
- will be hardened by heat treatment, max. hardness 57 HRC
- poor resistance to corrosion
- used where strength and/or hardness are of primary concern
- typical applications include tweezers and cutting tools for the electronic industry, watch-makers, jewelers applications

Composition

Component	Wt.%	Component	Wt.%	Component	Wt.%
С	0.57-0.65	Si	0.15-0.35	Cr	≤0.4
P	≤0.035	s	≤0.035		

Mechanical properties

Density	7.9 g/cm ³
Hardness, Vickers	700 HV
Tensile strength, ultimate	850-1000 MPa
0.2% Yield stress	500 MPa
Modulus of elasticity	200 GPa

Thermal properties

Coef. of lin. therm expansion	11 E-6/°C	20°C-100°C
Coef. of lin. therm expansion	12 E-6/°C	20°C-300°C
Specific heat capacity	0.502 J/(g K)	
Thermal conductivity	52 W/(m K)	

Electrical properties

0.18 E-4 Ohm.cm Resistivity

This document contains information based on average values as obtained from the results of laboratory tests and observations made on the material. Ideal-Tek SA declines all responsibility from an improper use of the product described in this document.

