





Datasheet

RS PRO 60W Switching Power Supply

Stock number: 139-2356

EN



Mechanical specification:

PSU housing:
Colour: black
Flammability rating: UL94V-0

Input connector: 2 wire non-grounding
type IEC320-C8

Output lead:
Type: UL2468 20AWG
Length: 1500mm +/- 20mm
Output connector: 2.1x5.5x12mm, centre +.

Mass: 0.24kg
Tolerance on dimensions: +/- 0.5mm unless stated otherwise



Safety specification:

Primary circuit protection: over current sensor.

Over current protection: 3.0 - 3.7A (with nominal input voltage): PSU will recover once excess load has been removed.

Short circuit protection: PSU will recover once short circuit has been removed.

MTBF: 50,000 hours (25°C) in accordance with Telcordia SR-332

Operating temperature range: -20°C to +40°C

Storage temperature range: -20°C to +85°C

Operating humidity range: 20% - 80% R.H.

Storage humidity range: 5% - 95% R.H.

Adaptor meets the following standards:

Level VI energy efficiency

EN60950

EN55022 class B

FCC part 15 class B

EN55024/A1:2001

IEC61000-4-11, IEC 61000-4-6

IEC61000-4-5, IEC61000-4-4

IEC61000-4-3, IEC61000-4-2

Electrical specification:

Input: 90-264V, 47/63Hz

Nominal full load input current: 2A max.

Inrush current (cold start): 50A max.

Nominal efficiency @ 230V: 89.19%

Off load stand-by power: 0.1W max.

Output voltage (+/-5%): 24VDC

Maximum output current: 2500mA

Load regulation: 5%

Ripple*: 150mVp-p

Hi-pot, primary to secondary: 3.75kVRMS / 10mA / for 60 seconds

Leakage current: 0.25mA max. @ 264VAC, 50Hz

Surge test: 3kV, common mode with varying phases 0°, 90°, 180°, 270° in accordance with EN61000-4-5:2006

Insulation breakdown, primary to secondary @ 500VDC: 50M ohms min.

*Ripple and noise: measurement is done with 20MHz bandwidth oscilloscope, 0.1uF ceramic capacitor in parallel with 47uF electrolytic capacitor.