



For more Information
please call

1-800-Belden1



General Description:

20 AWG solid .032" bare copper conductor, gas-injected foam HDPE insulation, Duofoil® + tinned copper braid shield (95% coverage), PVC jacket.

Usage (Overall)

Suitable Applications: SMPTE 2081-1 6 Gb/s UHDTV, SMPTE 424M 3 Gb/s HD-SDI 1080p

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	20	Solid	BC - Bare Copper	0.8128

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FHDPE - Foam High Density Polyethylene	3.683

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 5.918 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 46.134 Kg/Km

Max. Recommended Pulling Tension: 231.306 N

Min. Bend Radius/Minor Axis: 63.500 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMR

CEC/C(UL) Specification: CMG

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

RG Type: 59/U

Flame Test

UL Flame Test: UL1666 Vertical Shaft

CSA Flame Test: FT4

Suitability

Suitability - Indoor: Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Plenum Number: 1506A

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Inductance:

Inductance (µH/m)

0.351067

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

53.4803

Nominal Velocity of Propagation:

VP (%)

82.000

Nominal Delay:

Delay (ns/m)

4.068

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

32.81

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

12.4678

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1.000	0.984
3.600	1.969
5.000	2.067
6.000	2.264
7.000	2.428
10.000	2.953
12.000	2.986
25.000	4.265
67.500	6.726
71.500	6.890
88.500	7.218
100.000	7.546
135.000	8.859
143.000	9.187
180.000	10.171
270.000	12.468
360.000	14.436
540.000	18.046
720.000	20.998
750.000	21.327
1000.000	24.936
1500.000	31.170
2000.000	36.747
2250.000	39.044
3000.000	45.934
4500.000	57.418
6000.000	69.229

METRIC MEASUREMENT VERSION

1505A Coax - RG-59/U Type

Max. Operating Voltage - UL:

Voltage
300 V RMS

Other Electrical Characteristic 1: TDR Impedance: 75 +/- 1.5 Ohms

Other Electrical Characteristic 2: Return Loss: Fixed bridge and termination.

Minimum Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
5.000	1600.000	23.000
1600.000	4500.000	21.000
4500.000	6000.000	15.000

Sweep Test

Sweep Testing: 100#37; Sweep tested 5 MHz to 6 GHz.

Misc. Information (Overall)

Notes (Overall)

Notes: Also available in 4.5 GHz multi-coax bundled versions. See 7794A through 7796A, 7798A.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1505A N3UN1000	1,000 FT	36.000 LB	GREEN, MIL		#20 PE/GIFHDPE SH FRPVC
1505A N3U1000	1,000 FT	35.000 LB	GREEN, MIL	C	#20 PE/GIFHDPE SH FR PVC
1505A N3U5000	5,000 FT	165.000 LB	GREEN, MIL	C N	#20 PE/GIFHDPE SH FR PVC
1505A 001N1000	1,000 FT	36.000 LB	BROWN		#20 PE/GIFHDPE SH FRPVC
1505A 0011000	1,000 FT	35.000 LB	BROWN	C	#20 PE/GIFHDPE SH FR PVC
1505A 0015000	5,000 FT	165.000 LB	BROWN	C N	#20 PE/GIFHDPE SH FR PVC
1505A 002N1000	1,000 FT	36.000 LB	RED		#20 PE/GIFHDPE SH FRPVC
1505A 0021000	1,000 FT	35.000 LB	RED	C	#20 PE/GIFHDPE SH FR PVC
1505A 002500	500 FT	17.500 LB	RED	C	#20 PE/GIFHDPE SH FR PVC
1505A 0025000	5,000 FT	165.000 LB	ORANGE	C N	#20 PE/GIFHDPE SH FR PVC
1505A 003N1000	1,000 FT	36.000 LB	ORANGE		#20 PE/GIFHDPE SH FRPVC
1505A 0031000	1,000 FT	35.000 LB	ORANGE	C	#20 PE/GIFHDPE SH FR PVC
1505A 0035000	5,000 FT	165.000 LB	ORANGE	C N	#20 PE/GIFHDPE SH FR PVC
1505A 004N1000	1,000 FT	36.000 LB	YELLOW		#20 PE/GIFHDPE SH FRPVC
1505A 0041000	1,000 FT	35.000 LB	YELLOW	C	#20 PE/GIFHDPE SH FR PVC
1505A 0045000	5,000 FT	165.000 LB	YELLOW	C N	#20 PE/GIFHDPE SH FR PVC
1505A 006N1000	1,000 FT	36.000 LB	BLUE, LIGHT		#20 PE/GIFHDPE SH FRPVC
1505A 0061000	1,000 FT	35.000 LB	BLUE, LIGHT	C	#20 PE/GIFHDPE SH FR PVC
1505A 006500	500 FT	17.500 LB	BLUE, LIGHT	C	#20 PE/GIFHDPE SH FR PVC
1505A 0065000	5,000 FT	165.000 LB	BLUE, LIGHT	C N	#20 PE/GIFHDPE SH FR PVC
1505A 007N1000	1,000 FT	36.000 LB	VIOLET		#20 PE/GIFHDPE SH FRPVC
1505A 0071000	1,000 FT	35.000 LB	VIOLET	C	#20 PE/GIFHDPE SH FR PVC
1505A 0075000	5,000 FT	165.000 LB	VIOLET	C N	#20 PE/GIFHDPE SH FR PVC
1505A 008N1000	1,000 FT	36.000 LB	GRAY		#20 PE/GIFHDPE SH FRPVC
1505A 0081000	1,000 FT	35.000 LB	GRAY	C	#20 PE/GIFHDPE SH FR PVC
1505A 0085000	5,000 FT	165.000 LB	GRAY	C N	#20 PE/GIFHDPE SH FR PVC
1505A 009N1000	1,000 FT	36.000 LB	WHITE		#20 PE/GIFHDPE SH FRPVC
1505A 0091000	1,000 FT	35.000 LB	WHITE	C	#20 PE/GIFHDPE SH FR PVC
1505A 0095000	5,000 FT	165.000 LB	WHITE	C N	#20 PE/GIFHDPE SH FR PVC
1505A 010N1000	1,000 FT	36.000 LB	BLACK		#20 PE/GIFHDPE SH FRPVC
1505A 0101000	1,000 FT	35.000 LB	BLACK	C	#20 PE/GIFHDPE SH FR PVC
1505A 010500	500 FT	17.500 LB	BLACK	C	#20 PE/GIFHDPE SH FR PVC
1505A 0105000	5,000 FT	165.000 LB	BLACK	C N	#20 PE/GIFHDPE SH FR PVC

Notes:

C = CRATE REEL PUT-UP.

N = FINAL PUT-UP LENGTH MAY VARY -0% TO +10% FROM LENGTH SHOWN.

Revision Number: 10 Revision Date: 06-17-2016

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities

METRIC MEASUREMENT VERSION

1505A Coax - RG-59/U Type

and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).