

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Connector, 5-position, shielded, Socket straight M12, A-coded, Push-in connection, knurl material: Zinc diecast, nickel-plated, external cable diameter 4 mm ... 8 mm

## Your advantages

- ☑ Reliable and quick connection of electric cables
- Flexible signal and data cabling
- Quick and easy installation, thanks to Push-in connection technology



## **Key Commercial Data**

Packing unit	1 pc
GTIN	4 055626 375878
GTIN	4055626375878
Weight per Piece (excluding packing)	41.900 g
Custom tariff number	85366990
Country of origin	Germany

## Technical data

### **Dimensions**

Diameter housing	19 mm
Length	59 mm
External cable diameter	4 mm 8 mm
Stripping length of the sheath	29 mm
Stripping length of the individual wire	8 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C 85 °C (Plug / socket)



## Technical data

## Ambient conditions

Degree of protection	IP65
	IP67

## General

4 A
60 V DC
48 V AC
5
≥ 100 MΩ
A - standard
M12 connector IEC 61076-2-101
Shock, vibration EN 50155:2001
No
II II
3
Push-in connection
0.14 mm <sup>2</sup> 0.75 mm <sup>2</sup> (without ferrule)
0.08 mm² 0.5 mm² (with ferrule)
0.14 mm <sup>2</sup> 0.75 mm <sup>2</sup> (solid)
26 18 (without ferrule)
28 20 (with ferrule)
≥ 100
0.4 Nm (M12 knurl)
0.8 Nm (Connector with coupling sleeve)
3 Nm (Pressure nut with coupling sleeve)
The wires can be connected both with ferrules and without ferrules

## Material

Flammability rating according to UL 94	V0	
Contact material	CuSn	
Contact surface material	Ni/Au	
Contact carrier material	PA 6.6	
Material of grip body	Zinc die-cast, nickel-plated	
Material, knurls	Zinc die-cast, nickel-plated	
Sealing material	NBR	
Additional material specifications	TPE-U (Clamping cage, weight: 1.1 g)	
	PA 6 (Actuation lever)	
Standards/regulations	PA 6.6: Fire protection in rail vehicles - requirement sets R22, R23, R24 R25, and R26 acc. to DIN EN 45545-2 (Risk level HL1 - HL3)	
	PA 6: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3)	

Standards and Regulations



## Technical data

## Standards and Regulations

Standard designation	M12 connector
Standards/regulations	IEC 61076-2-101
Standard designation	Shock, vibration
Standards/regulations	EN 50155:2001
Flammability rating according to UL 94	V0

### **Environmental Product Compliance**

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values


## **Drawings**

### Schematic diagram




Pin assignment M12 socket, 5-pos., A-coded, socket side view

## Functional drawing



Slide the pressure nut and sleeve housing along the cable, strip the cable, shorten the shield, strip the single wires, connect the wires, in the case of a straight sleeve housing gently twist the wires together, stick the shielding foil around the shortened shield, in the case of a cable outside diameter < 6 mm stick an additional shielding foil around the wire pack, screw the sleeve housing to the plug insert, screw the pressure nut tight.

### Dimensional drawing





## Classifications

## eCl@ss

eCl@ss 5.1	27143423
eCl@ss 6.0	27279200
eCl@ss 7.0	27440104
eCl@ss 8.0	27440104
eCl@ss 9.0	27440102

## **ETIM**

ETIM 5.0	EC002635
ETIM 6.0	EC002635

## Approvals

Approvals

Approvals

EAC / UL Listed / cUL Listed / cULus Listed

Ex Approvals

## Approval details

EAC RU C-DE.AI30.B.01102

UL Listed	UL	http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm		E221474
Nominal voltage UN			60 V	
Nominal current IN			4 A	
mm²/AWG/kcmil			26-18	

cUL Listed	CUL	http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm		E221474
Nominal voltage UN			60 V	
Nominal current IN			4 A	
mm²/AWG/kcmil			26-18	



## **Approvals**

cULus Listed



## Accessories

Accessories

Cable by the meter

Cable reel - SAC-5P-100,0-PUR/SH-0,34 - 1501728



Cable ring, PUR halogen-free black, 5-pos., shielded, conductor colors: Brown/white/blue/black/gray, cable length:

#### Connector

Ferrule - AI 0,25- 6 YE - 3203024



Ferrule, sleeve length: 6 mm, length: 10.5 mm, color: yellow

## Ferrule - A 0,25-7 - 3202478



Ferrule, length: 7 mm, color: silver

### Ferrule - A 0,34-7 - 3009202



Ferrule, length: 7 mm, color: silver



### Accessories

Ferrule - A 0,5 - 6 - 3200218



Ferrule, length: 6 mm, color: silver

Ferrule - AI 0,5 - 6 WH - 3200687



Ferrule, sleeve length: 6 mm, length: 12 mm, color: white

### Crimping tool

Crimping pliers - CRIMPFOX 6H - 1212046



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.14 mm<sup>2</sup> ... 6 mm<sup>2</sup>, unlockable pressure lock, lateral entry

### Protective cap

Screw plug - PROT-M12 MS-PA-CHAIN - 1430899

M12 sealing cap with fixing band, for sensor cables, for free M12 sockets



### Screwdriver tools

Tool - SACC BIT M12-D20 - 1208445



Nut for assembling M12 connectors for assembly with a knurl diameter of 20 mm, for 4 mm hexagonal drive



### Accessories

Adapter insert - TSD-M SAC-BIT ADAPTER - 1212600



Adapter bit for TSD-M...torque tools, E6.3-1/4" drive with 4 mm hexagon to accommodate SAC bits

### Shield connection

Shielding foil - ALU-SB - 1404531

Shielding foil, for fixing the braided shield of shielded cables. Length: 4 cm, width: 1.2 cm



### Stripping tool

Stripping tool - WIREFOX 2,5 - 1212368



Stripping tool, for conductors and cables with a conductor cross section from 0.08 to 2.5 mm, self-adjusting, stripping length adjustable up to 15 mm, cutting capacity up to 6 mm² stranded/1.5 mm² solid

### Torque tool

Torque screwdriver - TSD 04 SAC - 1208429



Torque screwdriver, with preset torque of 0.4 Nm and 4 mm hexagonal drive for M12 connectors

Torque screwdriver - TSD 08 SAC - 1212597



Torque screw driver with preset torque of 0.8 Nm, with 4 mm hexagon for accommodating SAC bits, two-component handle with non-slip grip



## Accessories

Torque screwdriver - TSD-M 1,2NM - 1212224



Torque screw driver, accuracy as per EN ISO 6789 standard, adjustable from 0.3 - 1.2 Nm

Torque screwdriver - TSD-M 3NM - 1212225



Torque screw driver, accuracy as per EN ISO 6789 standard, adjustable from 1.2 - 3 Nm

Stripping tool - VS-CABLE-STRIP-VARIO - 1657407



Stripping tool, for the multi-level stripping of shielded cables

Phoenix Contact 2019 © - all rights reserved http://www.phoenixcontact.com