

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)

Flush-type connector, Power, 4-position, Plug, straight, M12, L-coded, Solder pins

\_\_\_\_\_

## Your advantages

- Easy PCB assembly: one-piece connectors for wave soldering
- For compact devices: transmit high power in a confined space
- Easy-to-install, optimized XL housing contour with wrench size 19
- Mechanical tightening limitation for long-term-stable gasket



### Key Commercial Data

Packing unit	20 pc
Minimum order quantity	20 pc
GTIN	4 055626 428451
GTIN	4055626428451
Weight per Piece (excluding packing)	17.800 g
Custom tariff number	85366990
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Ambient conditions

Ambient temperature (operation)	-25 °C 85 °C (Plug / socket)
	-40 °C 85 °C (without mechanical actuation)
Degree of protection	IP67
General	



## Technical data

### General

	there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Rated current at 40°C	16 A
Rated voltage	63 V
Rated surge voltage	1.5 kV
Number of positions	4
Coding	L - Power
Standards/regulations	M12 connector IEC 61076-2-111 In line with
Signal type/category	Power
Overvoltage category	
Degree of pollution	3
Connection method	Solder pins
Material	
Flammability rating according to UL 94	V0
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA
Material, knurls	Zinc die-cast, nickel-plated
Additional material specifications	PU 2K (Grout material)
Cable	
Standards/specifications	M12 connector IEC 61076-2-111 In line with
Standards and Regulations	
Standard designation	M12 connector
Standards/regulations	IEC 61076-2-111
Flammability rating according to UL 94	V0
t	

### **Environmental Product Compliance**

REACh SVHC	Lead 7439-92-1	
China RoHS	Environmentally Friendly Use Period = 50	
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"	

## Drawings



Dimensional drawing



Dimensional drawings can be found under Downloads

Schematic diagram



Pin assignment of M12 connector, 4-pos., L-coded, pin side view

### Classifications

#### eCl@ss

eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 8.0	27440102
eCl@ss 9.0	27440102

## Approvals

### Approvals

Approvals

cULus Recognized

#### Ex Approvals

Γ

### Approval details

cULus Re	cognized	c <b>AL</b> us	http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm E468743-20180113		
Nominal voltag	ge UN			63 V	
Nominal curre	nt IN			16 A	

### Accessories

Accessories

Protective cap

٦



### Accessories

Sealing cap - PROT-M12 FS - 1560251



M12 sealing cap for unoccupied M12 plugs of the sensor/actuator cable, flush-type plugs and I/O devices in the field

Sealing cap - PROT-M12 FS-M - 1430488



M12 metal sealing cap for unoccupied M12 plugs of the sensor/actuator cable, flush-type plugs and I/O devices in the field

Phoenix Contact 2019 © - all rights reserved http://www.phoenixcontact.com