



## Datasheet Stock No: 144-1597 144-1598 144-1599 144-1600 RS Pro RFT Interface Relay



### **Specifications:**

- 1 pole 12A
- Slim and compact size
- High Capacity and high reliability
- Meets with RoHs requirements
- With Lockable Test Button
- Double side LED integrated in relay
- With inspection window





# ENGLISH

RS Stock No		144-1597	144-1598	144-1599	144-1600
Characteristics					
Nominal Voltage		12VAC	24VAC	110VAC	230VAC
Options		LED + Locking Button	LED + Locking Button	LED + Locking Button	LED + Locking Button
Contact -	Configuration	Single Pole Change Over			
	Rated Current	12A/250VAC, 30VDC			
	Motor Load	1/3HP, 240VAC			
	Switching Capacity (resistive)	3000VA, 360W			
	Initial Contact Resistance	≤50mΩ			
	Material	Ag alloy			
	Electrical Durability	≥10 <sup>5</sup> times (1800 Ops/h)			
	Mechanical Durability	≥10 <sup>7</sup> times (18000 Ops/h)			
Pick-up Voltage (23°C)		AC: ≥80% (rated voltage)			
Drop-out Voltage (23°C)		AC: ≥30% (rated voltage)			
Maximum Voltage (23°C)		110% rated voltage			
Insulation resistance		≥1000mΩ (500VDC)			
Coil Operating _	DC (W)	0.53			
	AC (VA)	1			
Operating Time (at nominal voltage)		≤20ms			
Release Time (at nominal voltage)		≤10ms			
Initial Breakdown Voltage	Between open contacts	1000VAC/1min			
	Between Poles	1000VAC/1min			
	Between contacts and coil	5000VAC/1min			
Ambient Temperature		-40~+55°C			
Humidity		35%~85%RH			
Air Pressure		86~106KPa			
Shock Resisance		10G			
Vibration Resistance		10~55Hz double-amplitude: 1.0mm			
Mounting		Plug-in			
Unit Weight		Approx. 20g			
Certification					





## ENGLISH

#### Mounting Dimensions (mm)

