


LED Ecobasic A60 E27 DIM 8.5W (60W) 806lm 827 Opal

Article number 145678

BAI Ecobasic LED GLS A60 E27 8.5W 2700K Opal 806lm (60W) Dimmable 230-240V 200° 60x110mm LED-lamp

Because these low-budget lamps are very durable due to their low consumption and long lifespan, they are both ECOlogical and ECONomic. This version of the Ecobasic is dimmable. Use the correct LED dimmer. Ambient temperature range: -15°C to +40°C.



General ETIM properties

ETIM group	Lamps
ETIM class	LED-lamp/Multi-LED
Name	145678
Brand	Bailey
Productseries	Ecobasic LED bulb
Product type	A60 DIM

ETIM specifications

IFTTT support available	No
Compatible with Amazon Alexa	No
Compatible with Google Assistant	No
Compatible with Apple HomeKit	No
Photobiological safety according to EN 62471	RG1
With remote control	No
Remote operation possible	No
Average nominal lifespan [h]	15000
Weighted energy consumption in 1000 hours [kWh]	9
Min. number of switching cycles	15000
Energy efficiency class	F
Lamp designation	A-type
Degree of protection (IP)	IP20
Length [mm]	110
Diameter [mm]	60
Dimmable	Yes
Colour consistency (McAdam ellipse)	SDCM6
Beam angle [°]	200 - 200
Colour housing	White
Colour temperature [K]	2700 - 2700
Colour	White
Socket	E27
Colour of light according to EN 12464-1	Warm white <3300 K
Type of glass/cover	Opal
Filament lamp	No
Lamp shape	Pear-shape
Colour rendering index CRI	80-89
Lamp efficacy [lm/W]	90
Luminous flux [lm]	806 - 806
Voltage type	AC
Lamp power [W]	8.5 - 8.5
Power factor	0.7
Nominal current [mA]	50 - 50
Nominal voltage [V]	220 - 240