



LED Corn Switch E40 80W-120W 10800-17400lm 3000K-5000K


Article number 145792

BAI LED Corn Switch E40 3CCT 80W=10800lm 100W=14000lm 120W=17400lm 3000K 4000K 5000K 100V-260V 360° 130x285mm IP64 120V-130V 230V-240V DISCONNECT BALLAST

Sustainability is not only about replacing old light sources with a more energy-efficient version, but also about reusing existing fixtures. It is even more sustainable when 9 different versions are combined in 1 product. This saves on transport and storage. The special thing about the Switch series is that by simply adjusting a switch, the power (80W, 100W or 120W) and the light color can change (3000K, 4000K or 5000K). That's Smart and Green Thinking. Installation: disconnect the ballast before use. AC 100-260V 50/60Hz. Burning position: universal. Only suitable for temperatures up to 45°C inside the fixture. The LED light source can quickly malfunction due to overheating. Therefore not suitable for use in tight fixtures or fixtures where the reflector is close to the LED Corn. Recommended to remove glass or cover from the fixture.



ledcorn



General ETIM properties

ETIM group	Lamps
ETIM class	LED-lamp/Multi-LED
Name	145792
Brand	Bailey
Productseries	LED Corn
Product type	Switch

ETIM specifications

Nominal voltage [V]	100 - 260
Nominal current [mA]	1333 - 1333
Power factor	0.9
Lamp power [W]	80 - 120
Voltage type	AC
Luminous flux [lm]	10800 - 17400
Lamp efficacy [lm/W]	145
Colour rendering index CRI	80-89
Lamp shape	Tube, single-ended
Filament lamp	No
Type of glass/cover	Clear
Colour of light according to EN 12464-1	Neutral white 3300-5300 K
Socket	E40
Colour	White
Colour temperature [K]	3000 - 5000
Colour housing	White
Beam angle [°]	360 - 360
Colour consistency (McAdam ellipse)	SDCM4
Dimmable	No
Diameter [mm]	130
Length [mm]	285
Degree of protection (IP)	IP64
Lamp designation	Other
Energy efficiency class	D
Min. number of switching cycles	12000
Weighted energy consumption in 1000 hours [kWh]	120
Average nominal lifespan [h]	50000
Remote operation possible	No
With remote control	No
Photobiological safety according to EN 62471	RG0
Compatible with Apple HomeKit	No
Compatible with Google Assistant	No
Compatible with Amazon Alexa	No
IFTTT support available	No