WHEN PERFORMANCE MATTERS MOST

TECHNICAL DATA SHEET

TagLock[™] Securing Device for Single Pole Breakers

Catalog #: 148696, 148688 & 148700

Design

- For use on Square D NQO and other breakers that have a hole in the switch tongue
- Align pins with hole and snap closed, where the pins are preventing the switch from being moved to the "ON" position
- Secure with 50 lb. minimum strength non-releasable nylon fasteners (shown) or padlock
- Made of impact modified nylon





www.bradyid.com

Material

- Slide, Residential Glass filled Nylon
- Color: Red, PMS 1805 C
- Body Glass-filled Nylon
- Color: Black
- Spring form stainless steel
- Fastener Nylon
- UL Rating: UL 94 HB

Chemical	°C	Chemical	°C
Acetone	25	Petroleum	25
Acetone	60	Turpentine oil	25
Chlorine, chlorine water	25	Turpentine substitute (white spirit)	25
Fuel, engine: Gasoline (normal & premium grade)	85	Trichloroethane 1,1,1	45
Lubrication oil: gear oil	< 120	Lubricating oil: HD engine oils, hydraulic oils, transformer oils	< 120
Fuel, engine: M15 mixture (15% methanol)	70	Water (including seawater)	25
Methanol	25	Water (including seawater), chlorinated (<0,5 mg/l)	80

Temperature Range


Glass-filled Nylon: -20° to 120°C (0° to 250°F)

Chemical Resistance

All approved chemicals listed are based on the manufactures specified chemical resistance chart for plastic material only.

Dimensions

0.740" [18.8mm]
0.934" [23.7mm]
1.991" [50.6mm]
0.300" [7.6mm]
2.446" [62.1mm]



North America LEEEE W. Cood Hope Rd | Milwaukoo W/ 53232 | USA | Tol: 414 358 6600 | Eav. 414 328 5770

Y4282457

Circuit Breaker Cross Reference Guide

Circuit Breaker Manufacture	Breaker Type	" of Poles
American Switch	С	1
Cutler Hammer	СН	1
Cutler Hammer	СНВ	1
Cutler Hammer	CHP	1
Cutler Hammer	CHQ	1
Cutler Hammer	CL	1
Siemans ITE	BL	1
Square D	QO	1
Square D	QO	2-3
Square D	QOB	1
Square D	QOB	2-3
Square D	QOB-H	2
Square D	QOB-VH	1
Square D	QO-H	2
Square D	QO-SWN	2-3
Square D	QOU	1
Square D	QOU	2-3
Square D	QO-VH	1
Square D	QO-VH	2-3
Square D	QYU	1

Brady North America | 6555 W. Good Hope Rd | Milwaukee, WI 53223 | USA | Tel: 414-358-6600 | Fax: 414-228-5770

Y4282457

MSDS Information

1. HAZARDS IDENTIFICATION

This product is NOT DANGEROUS and contains no hazardous ingredients.

2. FIRST AID MEASURES/HEALTH INFORMATION /PROTECTION

Eye Contact:	Not applicable, product is inert
Ingestion:	Not applicable, first aid is not normally required.
Inhalation:	Not applicable
Skin Contact:	Not applicable, product is inert, except if product is melted use gloves. For hot melted product, immerse in or flush affected area with water to dissipate heat, then obtain medical attention.
Exposure Limits:	None
Threshold Limits	None
Personal Protection:	None (ambient conditions)
NPCA-HMIS Rating:	Health: 0; Flammability: 1; Reactivity: 0
NFPA-704 Rating:	Health: 0; Flammability: 1; Reactivity: 0

3. FIRE-FIGHTING MEASURES

Be cautious of hot melted Nylon	 Use water spray to cool fire, exposed surfaces, and to protect personnel
Isolate product from fire	 Respiratory and eye protection is required for fire fighting personnel
• Extinguish fire with water spray	 Decomposition products under fire conditions: Oxygen-lean conditions may cause monoxide and irritating smoke

4. ACCIDENTAL RELEASE MEASURES

Land	Recover material and place in suitable container for reuse or for disposal in conformance with local regulations.
Water	Recover material and place in suitable container for reuse or for disposal in conformance with local regulations.

5. HANDLING AND STORAGE

5.1 Handling	5.2 Storage
No precautions noted-see local regulation if needed	Storage pressure: Atmospheric
	Storage temperature: Ambient, no direct sunlight

6. EXPOSURE CONTROLS/PERSONAL PROTECTION

6.1 Exposure limit values	6.2 Exposure Controls
None	6.2.1 Occupational Exposure Controls
	6.2.1.1 Respiratory Protection: Not applicable
	6.2.1.2 Hand Protection: Not applicable
	6.2.1.3 Eye Protection: Not applicable
	6.2.1.4 Skin Protection: Not applicable
	6.2.2 Environmental Exposure Controls: No data available

7. PHYSICAL AND CHEMICAL PROPERTIES

General Information	
Other Information	

8. STABILITY AND REACTIVITY

8.1	Conditions to Avoid
	Higher Temperatures and direct sunlight (chemical resistance is excellent)
	Highly stable, but temperatures over 480 F may cause degradation
8.2	Materials to Avoid
	No data available
8.3	Hazardous Decomposition Products
	Under fire and oxygen-lean conditions may cause monoxide and irritating smoke

MSDS Information (continued)

9. ECOLOGICAL INFORMATION

9.1 Ecotoxicity	No data available
9.2 Mobility	No data available
9.3 Persistence and Degradability	No data available
9.4 Bioaccumulative Potential	No data available
9.5 Other Adverse Effects	No data available

10. DISPOSAL CONSIDERATIONS

None of the materials in this product are Recyclable, dispose of all materials in accordance with an applicable federal, state, and local law.

11. TRANSPORT INFORMATION

No data available

12. REGULATORY INFORMATION

This product has been tested and validated to the Regulatory Requirements listed below:		
 OSHA 29 CFR 1910.147 ©(4)(ii)(A)(1)/(c)(5)(ii)(C)(1) 	ANSI Standard Z244	

13. OTHER INFORMATION

No data available

WARRANTY STATEMENT

Supplier warrants that all goods will be free from defects in materials and workmanship for a period of six (6) months from the time of delivery to the consumer by Supplier. Repair, replacement or credit (at Supplier's option) upon return of the goods is Purchaser's sole remedy for any such losses, expenses, inconveniences or damages. The limited warranty does not apply if (1) the defect is the result of use or handling of the goods in a manner, circumstance, or purpose other than those approved or instructed by Supplier, as identified in the installation procedures accompanying the product, the instruction for use found on the product and as found on the Brady's website; or (2) the goods are misused or abused or there is evidence of tampering, mishandling, neglect, accidental damages, modifications or repair without the approval of Supplier.

Copyright 2019 Brady Worldwide, Inc. | All Rights Reserved Material may not be reproduced or distributed in any form without written permission.