




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: 1 – 2.5 mm<sup>2</sup>

Mating Tab Width: 6.35 mm [.25 in]

Mating Tab Thickness: .81 mm [.032 in]

## Features

### Product Type Features

Insertion Force	Normal
-----------------	--------

### Configuration Features

Connection Capacity	Single
Compatible With Wire & Cable Type	Discrete Wire

### Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm [.25 in]
Mating Tab Thickness	.81 mm [.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

### Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

### Mechanical Attachment

Extraction Force	80 Newton
------------------	-----------

Wire Insulation Support	With
-------------------------	------

Mating Retention Type	Dimple
-----------------------	--------

### Dimensions

Terminal Material Thickness	.41 mm[.016 in]
-----------------------------	-----------------

Product Length	19.1 mm[.751 in]
----------------	------------------

Compatible Insulation Diameter Range	3.1 – 4.3 mm[.12 – .169 in]
--------------------------------------	-----------------------------

Wire Size	1 – 2.5 mm <sup>2</sup>
-----------	-------------------------

### Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
-----------------------------	----------------------------

### Industry Standards

Agency/Standard	CSA, UL
-----------------	---------

### Packaging Features

Packaging Quantity	6000
--------------------	------

Packaging Method	Strip/Reel
------------------	------------

### Other

Line	Premier
------	---------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 63648-1  
250 FASTON FLAG REC 20-14 AWG BR



TE Part # 180397-1  
250 FASTON, FLAG, REC., 17-14 AWG, BR



TE Part # 2-2150234-1  
OCEAN\_2.0\_APPLICATOR-E-110F180F



TE Part # 2-2150234-2  
OCEAN\_2.0\_APPLICATOR-E-110F180F



TE Part # 2150234-1  
OCEAN\_2.0\_APPLICATOR-E-110F180F



TE Part # 2150234-2  
OCEAN\_2.0\_APPLICATOR-E-110F180F



TE Part # 42239-4  
205 FASTON REC 18-14 AWG PHBZ



TE Part # 7-2150234-1  
OCEAN\_2.0\_APPLICATOR-E-110F180F



TE Part # 7-2150234-2  
OCEAN\_2.0\_APPLICATOR-E-110F180F




**KIT**  
REPRESENTATION ONLY

TE Part # 7-2150234-7  
OCEAN\_2.0\_SPARE\_PART\_KIT-110F180F

Also in the Series | **FASTON 250**



Compression Connectors(4)



Crimp Terminal Housings(139)



Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(135)



Quick Disconnects(444)




Splices(4)


## Customers Also Bought




TE Part #2-6609115-9  
6EGG8-2 S0=F7386B




TE Part #1-1586019-8  
18P RCPT VAL-U-LOK V0




TE Part #1586000-4  
4P FH PLUG VAL-U-LOK V2



TE Part #1-794953-8  
18P PM PLUG VAL-U-LOK V2




TE Part #794953-2  
2P PM PLUG VAL-U-LOK V2




TE Part #794953-6  
6P PM PLUG VAL-U-LOK V2




TE Part #2-31894-2  
PIDG 22-16 22-18MIL R 1/4;TAPE



TE Part #2820453010  
44A0111-24-5



TE Part #1586019-6  
6P RCPT VAL-U-LOK V0



TE Part #174929-1  
070 MLC W-W CAP HSG 4P NATURAL

## Documents



## Product Drawings

[250 FASTON,REC.,17-14 AWG,BR](#)

---

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_160808-2\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_160808-2\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_160808-2\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Product Specifications

[Application Specification](#)

English

---

### Product Environmental Compliance

[MD\\_160808-2\\_0505201664\\_dmtec](#)

English

[MD\\_160808-2\\_0505201664\\_dmtec](#)

English