




Power supply connectors



Power supply chassis socket, straight version, with solder eyes, for printed circuit boards, for front side mounting



16 1614 24



Environmental conditions

Temperature range	-30 °C/+70 °C	
Materials		
Insulating body	PBT, V-0 according to UL94	
Contact spring	CuZn, nickel-plated	
Contact pin	CuZn, nickel-plated	
Hexagonal nut	CuZn, nickel-plated	
Mechanical data		

Diameter opening	6.6 mm
Diameter center pin	2.5 mm
Mating cycles	5000 ¹
Insertion force	3–30 N
Withdrawal force	3–30 N
¹ gemessen mit einem Lehrenstecker	

Electrical data (at Tamb 20 °C)

Contact resistance	≤ 30 mΩ
Rated current	2 A
Rated voltage	30 V
Rated impulse voltage	500 V/60 s
Insulation resistance	≥ 100 MΩ


Associated products


Counterparts C 1633 04 🗗 NES/J 250

ي،5 ک

⊡ 1634 02 C XNES/J 250

🖙 NES/J 25





_____l⊸ 1 *a 0,6

*a printed circuit board layout





Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
1614 24	2	500	1000

Packaging:

in bulk, in a cardboard box or a plastic bag