




A Dimensions: [mm]












Scale - 20:

B Recommended land pattern: [mm]




Scale - 20:1

WÜRTH ELEKTRONIK

D Absolute Maximum Ratings (Ambient Temperature 25°C):

Properties	Test conditions		Value	Unit
Power dissipation		P _{Diss}	105	mW
Peak Forward Current	duty/10@1kHz	I _{F Peak}	100	mA
Continuous Forward Current		Ι _F	30	mA
Reverse Voltage		V _{Rev}	5	V
ESD Threshold/ Human Body Modell		V _{ESD} HBM	1000	V

C Schematic:



E General information:

•Operating temperature: -40°C to +85°C

•Storage temperature (sealed bag): -40°C to +85°C; 60% RH max.

Optical Properties:

Properties	Value
Chip Technology	InGaN
Emitting Color	Blue
Lens Type	Chip LED

				Pr
2.6	2014-03-13	SSt	SSt] _
2.5	2013-12-09	SSt	H0e	
2.4	2013-10-08	SSt	H0e	W
2.3	2013-09-10	SSt	SSt	E! M
2.2	2013-04-10	SSt	SSt	74
2.1	2012-12-10	SSt	SSt	G Te
2.0	2012-11-05	SSt	H0e	w ei
REV	DATE	BY	CHECKED	61



Würth Elektronik eiSos GmbH & Co. KG
EMC & Inductive Solutions
Max-Eyth-Str. 1
74638 Waldenburg
Germany
Tel. +49 (0) 79 42 945 - 0
www.we-online.com
eiSos@we-online.com

DECODIDATION

WL-SMCW SMD chip LED top view monocolor waterclear

Order.- No.

150060BS75000



SIZE
A4



D Electrical & Optical Properties:

Properties	Test conditions			Value		Unit
Торогаоо	Tool conditions		min.	typ.	max.	O.I.I.
Peak Wavelength	20 mA	λ _{Peak}		465		nm
Dominant wavelength	20 mA	λ _{Dom}		470		nm
Luminous Intensity	20 mA	lV	90	145		mcd
Forward Voltage	20 mA	V _F		3.2	3.5	V
Spectral Bandwidth	20 mA	Δλ		25		nm
Reverse Current	5 V	I _{Rev}			10	μА
Viewing Angle	20 mA	2 θ _{50%}		140		0

				F
2.6	2014-03-13	SSt	SSt	
2.5	2013-12-09	SSt	H0e	
2.4	2013-10-08	SSt	H0e	١
2.3	2013-09-10	SSt	SSt	1
2.2	2013-04-10	SSt	SSt	7
2.1	2012-12-10	SSt	SSt	(
2.0	2012-11-05	SSt	H0e	١
REV	DATE	BY	CHECKED	,



Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com DESCRIPTION

WL-SMCW SMD chip LED top view monocolor waterclear

Order.- No.

Size: 0603


150060BS75000

ROHS&REACH HALOGENFREE


SIZE A4



F1 Viewing Angle:



F2 Spectral:



				Projection ,
2.6	2014-03-13	SSt	SSt	
2.5	2013-12-09	SSt	H0e	
2.4	2013-10-08	SSt	H0e	Würth Elektronik eiSos GmbH & Co. KG
2.3	2013-09-10	SSt	SSt	EMC & Inductive Solutions Max-Eyth-Str. 1
2.2	2013-04-10	SSt	SSt	74638 Waldenburg
2.1	2012-12-10	SSt	SSt	Germany Tel. +49 (0) 79 42 945 - 0
2.0	2012-11-05	SSt	H0e	www.we-online.com eiSos@we-online.com
RFV	DATE	BY	CHECKED	eloosewe-online.com

DESCRIPTION

WL-SMCW SMD chip LED top view monocolor waterclear

Order.- No


150060BS75000

ROHS&REACH HALOGENFREE


SIZE A4



F3 Forward Current vs. Forward Voltage:




F4 Luminous Intensity vs. Forward Current:




				Projection ,		DESCRIPTION					
2.6	2014-03-13	SSt	SSt	- -1	Sos GmbH & Co. KG ulutions 945 - 0						
2.5	2013-12-09	SSt	H0e	Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg	WL-SMCW SMD c	MD chip LED top view mono-					
2.4	2013-10-08	SSt	H0e	Würth Elektronik eiSos Gmb	H & Co. KG	color waterclear					
2.3	2013-09-10	SSt	SSt	EMC & Inductive Solutions		Color Watercical					
2.2	2013-04-10	SSt	SSt	74638 Waldenburg		Order No.	COMPLIANT	SI7F			
2.1	2012-12-10	SSt	SSt	Germany Tel. +49 (0) 79 42 945 - 0		450000000	ROHS&REACH HALOGENFREE	OIZE			
2.0	2012-11-05	SSt	H0e	www.we-online.com eiSos@we-online.com		150060BS75000	2 TIMES GETTI MEE	A4			
REV	DATE	BY	CHECKED	CIOCOSSWC OIIIIIG.COIII		Size: 0603		_			




F5 Derating Curve:




				Projection ,		DESCRIPTION					
2.6	2014-03-13	SSt	SSt								
2.5	2013-12-09	SSt	H0e	9		↓ WL-SMCW SMD chip LED top view mo					
2.4	2013-10-08	SSt	H0e	Würth Elektronik eiSos Gmbl	H & Co. KG	color waterclear					
2.3	2013-09-10	SSt	SSt	Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg	Color Watercical						
2.2	2013-04-10	SSt	SSt	74638 Waldenburg		Order No.	COMPLIANT	SIZF			
2.1	2012-12-10	SSt	SSt	Germany Tel. +49 (0) 79 42 945 - 0	el. +49 (0) 79 42 945 - 0 ww.we-online.com	450000000000000000000000000000000000000	ROHS&REACH HALOGENFREE	SIZL			
2.0	2012-11-05	SSt	H0e	www.we-online.com eiSos@we-online.com		150060BS75000	2 TIMES GETTI MEE	A4			
REV	DATE	BY	CHECKED	Cloudsewe offiliae.com		Size: 0603					






		A0	В0	w	P1	Т	T1	T2	D0	E1	E2	F	P0	P2	Таре	Packaging Unit
	tolerance	typ.	typ.	+0,3 -0,1	± 0,1	± 0,1	max.	typ.	+0,1 -0,0	± 0,1	min.	± 0,05	± 0,1	± 0,05		
a	0603	1,30	2,10	8,00	4,00	0,15	0,10	1,20	1,50	1,75	6,25	3,50	4,00	2,00	Polystyrene	4000
Size	0805	1,75	2,50	8,00	4,00	0,15	0,10	1,20	1,50	1,75	6,25	3,50	4,00	2,00	Polystyrene	4000
L	1206	2,10	3,70	8,00	4,00	0,15	0,10	1,20	1,50	1,75	6,25	3,50	4,00	2,00	Polystyrene	3000




Packaging is referred to the international standard IEC 60286 -3:2007




					Projection ,
	2.6	2014-03-13	SSt	SSt	- 1
	2.5	2013-12-09	SSt	H0e	9
	2.4	2013-10-08	SSt	H0e	Würth Elektronik eiSos
	2.3	2013-09-10	SSt	SSt	EMC & Inductive Solution Max-Eyth-Str. 1
	2.2	2013-04-10	SSt	SSt	74638 Waldenburg
	2.1	2012-12-10	SSt	SSt	Germany Tel. +49 (0) 79 42 945
e N	2.0	2012-11-05	SSt	H0e	www.we-online.com eiSos@we-online.com
-	REV	DATE	BY	CHECKED	CIOOSSWC-OIIIIIC.COIII



Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com



		Α	В	С	D	N	W1	W2	W3	W3
tolerance			min.	± 0,8	min.	min.	+ 1,5	max.	min.	max.
Tape width	8 mm	178,00	1,50	13,00	20,20	50,00	8,40	14,40	7,90	10,90



DESCRIPTION

WL-SMCW SMD chip LED top view monocolor waterclear

Order.- No.

Size: 0603

150060BS75000

COMPLIANT RoHS&REACh HALOGENFREE

A4


SIZE

This electronic component has been designed and developed for usage in general electronic equipment only. This product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik eiSos GmbH & Co KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, strip control), transportation (automotive control, train control, strip control), transportation (automotive control, train control, strip control), transportation (automotive control, train control, trai the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

H Soldering Specifications:



H1: Classification Reflow Profile for SMT components:



H2: Classification Reflow Profile:

Profile Feature	Pb-Free Assembly	
Preheat - Temperature Min (T _{smin}) - Temperature Max (T _{smax}) - Time (t _s) from (T _{smin} to T _{smax})	150°C 200°C 120 seconds max.	
Ramp-up rate (T _L to T _P)	3°C/ second max.	
Liquidous temperature (T_L) Time (t_L) maintained above T_L	217°C 60 seconds max.	
Peak package body temperature (T _p)	250°C max.	
Time within 5°C of actual peak temperature (tp)	10 seconds max.	
Ramp-down rate (T _P to T _L)	6°C/ second max.	
Time 25°C to peak temperature	220 seconds max.	
Applied cycles	2 cycles max.	

				Projection ,		
2.6	2014-03-13	SSt	SSt	1-1-6-	10.	
2.5	2013-12-09	SSt	H0e		No.	
2.4	2013-10-08	SSt	H0e	Würth Flektronik eiSos GmbH & Co. KG		
2.3	2013-09-10	SSt	SSt	EMC & Inductive Solutions Max-Evth-Str. 1		
2.2	2013-04-10	SSt	SSt	74638 Waldenburg		
2.1	2012-12-10	SSt	SSt	Germany Tel. +49 (0) 79 42 945 - 0		
2.0	2012-11-05	SSt	H0e	www.we-online.com eiSos@we-online.com		
REV	DATE	BY	CHECKED	GIOOSSWC GIIIIIG.COIII		

WL-SMCW SMD chip LED top view monocolor waterclear

Order.- No.

DESCRIPTION

150060BS75000



SIZE A4

This electronic component has been designed and developed for usage in general electronic equipment only. This product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use.

Moreover Würth Elektronik elSos GmbH & Co KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control in the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

I Cautions and Warnings:

The following conditions apply to all goods within the product series of WL-SMCW of Würth Elektronik eiSos GmbH & Co. KG:

General:

All recommendations according to the general technical specifications of the data sheet have to be complied with.

The usage and operation of the product within ambient conditions, which probably alloy or harm the component surface, has to be avoided.

If the product is potted in customer applications, the potting material might shrink during and after hardening. The product is exposed to the pressure of the potting material with the effect that the LED body, pins or termination is possibly damaged by this pressure and so the electrical as well as the mechanical characteristics are endangered to be affected. After the potting material is cured, the LED body, pins or termination of the product have to be checked if any reduced electrical or mechanical functions or destructions have occurred.

The responsibility for the applicability of customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products do also apply to customer specific products.

Washing varnish agent that is used during the production to clean the customer application might damage or change the characteristics of the LED body, pins or termination. The washing varnish agent could have a negative effect on the long term function of the product.

Direct mechanical impact to the product shall be prevented as the material of the LED body, pins or termination could flake or in the worst case it could break.

The standard deliveries include values in the range and limitation as defined in the Electrical & Optical Properties specified in the datasheet. On each reel, only one bin is sorted and taped. The bin is defined on intensity, chromaticity coordinate or wavelength and forward voltage. In order to ensure highest availability, the reel binning of standard deliveries can vary. A single bin cannot be ordered. Please contact us in advance, if you need a particular bin sorting before placing your order to clarify the lead time, MOQ and pricing.



Product specific:

Follow all instructions mentioned in the data sheet, especially:

- •The soldering profile has to be complied with according to the technical reflow/ or wave soldering specification, otherwise this will void the warranty.
- •All products shall be used before the end of the period of 12 months based on the product date code, if not a 100% solderability can't be quaranteed.
- Violation of the technical product specifications such as exceeding the absolute maximum ratings will void the warranty.
- •It is also recommended to return the LEDs to the original moisture proof bag and reseal the moisture proof bag again.
- Certain LED surfaces consist of soft material. Pressure on the top surface has to be handeled carefully to prevent negative influence to the function and reliability of the LEDs.
- •ESD prevention methods need to be applicated for manual handling and processing by machinery.
- Resistors for protection are obligatory.
- •Luminaires in operation could harm human vision or skin on a photo-biological level, therefore direct light impact has to be avoided. All products are additionally certified as risk groups 0 to 2 according to DIN EN 62471:2008

				Projection ,		Ī
2.6	2014-03-13	SSt	SSt		10.	l
2.5	2013-12-09	SSt	H0e			
2.4	2013-10-08	SSt	H0e	Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1		l
2.3	2013-09-10	SSt	SSt			l
2.2	2013-04-10	SSt	SSt	74638 Waldenburg		ſ
2.1	2012-12-10	SSt	SSt	Germany Tel. +49 (0) 79 42 945 - 0		l
2.0	2012-11-05	SSt	H0e	www.we-online.com eiSos@we-online.com		L
REV	DATE	BY	CHECKED	CIOCOSSWC OFFIIITIC.COTT		ſ

DESCRIPTION

WL-SMCW SMD chip LED top view monocolor waterclear

Order.- No.

Size: 0603

150060BS75000



SIZE A4

J Important Notes:

The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications.

In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component.

Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.



6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered.

The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG.

Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

				Projection ,		
2.6	2014-03-13	SSt	SSt	1-1-6	10.	
2.5	2013-12-09	SSt	H0e			
2.4	2013-10-08	SSt	H0e	Würth Elektronik eiSos GmbH & Co. KG		
2.3	2013-09-10	SSt	SSt	EMC & Inductive Solutions Max-Eyth-Str. 1		
2.2	2013-04-10	SSt	SSt	MAX-Eyur-Su. 1 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com		
2.1	2012-12-10	SSt	SSt			
2.0	2012-11-05	SSt	H0e			
REV	DATE	BY	CHECKED	CIOCOSSWC CITILITIC.COTT		

DESCRIPTION

WL-SMCW SMD chip LED top view monocolor waterclear

Order.- No.

Size: 0603

150060BS75000



SIZE A4

This electronic component has been designed and developed for usage in general electronic equipment where a higher safety standard and reliability standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use.

Moreover Würth Elektronik elSos GmbH & Co KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive real position), transportation signal, disaster prevention, medical, public information network etc.. Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.