




SFP28

TE Internal #: 1658862-1

SFP, SFP+ & zSFP+, Accessory, Data Rate (Max) 4 Gb/s, With Lightpipe, 2 x 1, All Four, Standard, Standard, 1 Port

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages > SFP, SFP+ & zSFP+ > SFP+ Stacked Cage Assemblies



Pluggable I/O Product Type: **Accessory**

Data Rate (Max): **4 Gb/s**

Lightpipe Options: **With Lightpipe**

Port Matrix Configuration: **2 x 1**

Lightpipe Configuration: **All Four**

[All SFP+ Stacked Cage Assemblies \(125\)](#)

Features

Product Type Features

| | |
|------------------------------|----------------|
| Form Factor | SFP |
| Pluggable I/O Accessory Type | Lightpipe Kit |
| Cage Type | Stacked |
| Pluggable I/O Product Type | Accessory |
| Lightpipe Options | With Lightpipe |
| Sealable | No |

Configuration Features

| | |
|---------------------------|----------|
| Port Matrix Configuration | 2 x 1 |
| Lightpipe Configuration | All Four |
| Lightpipe Style | Standard |
| Lightpipe Profile | Standard |
| Number of Ports | 1 |

Electrical Characteristics



| | |
|-----------------|--------|
| Data Rate (Max) | 4 Gb/s |
|-----------------|--------|

Operation/Application

| | |
|-------------------------------------|---------------------------|
| For Use With Pluggable I/O Products | Stacked SFP Cage Assembly |
|-------------------------------------|---------------------------|

Packaging Features

| | |
|------------------|------|
| Packaging Method | Tray |
|------------------|------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC |
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

SFP 2X1 LIGHT PIPE ASSY

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1658862-1_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1658862-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1658862-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English