

## TM-I TM-I 18 MC NE WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are five different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the SMark laser printer, PrintJet ADVANCED, plotter, MC-Mobilo or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

### General ordering data

Type	TM-I 18 MC NE WS
Order No.	<a href="#">1718431044</a>
Version	TM-I, Insert markers, 18 x 4 mm, white
GTIN (EAN)	4008190349011
Qty.	320 pc(s).
compatible printer	<a href="#">1324380000</a>

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**TM-I**  
**TM-I 18 MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	4 mm	Width (inches)	0.157 inch
Height	18 mm	Height (inches)	0.709 inch
Depth	1.7 mm	Depth (inches)	0.067 inch
Net weight	0.338 g		

**General data**

Colour code	white	Material	Polyamide 66
Material colour according to resistance code	9	Number per roll	64
Number per sheet	64	Operating temperature range	-40...100 °C
Recommended industries	Transportation, Machinery	Type of printing	blank
UL 94 flammability rating	V-2	Width	4 mm

**Conductor and cable markers**

Halogen	No
---------	----

**Classifications**

ETIM 3.0	EC001530	ETIM 4.0	EC001530
ETIM 5.0	EC001530	ETIM 6.0	EC001530
UNSPSC	44-12-17-08	eClass 5.1	27-14-91-03
eClass 6.2	27-40-04-01	eClass 7.1	27-14-91-03
eClass 8.1	27-14-91-03	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Brochure/Catalogue	<a href="#">CAT 9 IETH 15/16 EN</a> <a href="#">CAT 8 SAI 15/16 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>
Software	<a href="#">M-Print PRO configuration file</a>

**Data sheet**

**TM-I**  
**TM-I 18 MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

