




Datasheet Stock No.1875696,1875697,1875698,1875699 RS PRO MALE-FEMALE NON-RETURN VALVE





Code	Α	В	С	L	СН	Seal	Bag
	M5	5,5	4	34,5	8	NBR	10
1875696	1/8	8,5	6	37,5	14	NBR	10
1875697	1/4	11	8	46,5	17	NBR	10
1875698	3/8	12	9	61	24	NBR	10
1875699	1/2	15	10	64	24	NBR	10
	M5	5,5	4	34,5	8	FKM	10
	1/8	8,5	6	37,5	14	FKM	10
	1/4	11	8	46,5	17	FKM	10
	3/8	12	9	61	24	FKM	10
	1/2	15	10	64	24	FKM	10

The serie came up to answer the most estreme demands of pneumatic automation. It is a line in technopolymer, lighter and more compact which offers to demanding customers high performances. Wide Range Ø 2 - 14 mm.

Main advantages


- Quick connection and disconnection
- Full Flow and Vacuum resistant tank to special shaped seals
- 3 threads available, BSPP, BSPT (universal short) & Metric
- Lighter and More compact
- Specific configurations to satisfy the advanced robotics
- Silicon Free

Technical Characteristics

Component Parts and Materials

- **1** Nickel-plated brass Body
- 2 Acetalic resin Collet
- **3** Nickel-plated brass Capsule
- 4 Steel AISI 301 Clamping washer 5
- Technopolymeric positioning ring **6** NBR Molded seal
- 7 NBR Thread packing
- 8 Base Threaded Nickel Plated Brass
- 9 Technopolymeric Body PA
- 10 NBR seal

Reference standard





Compressed air / Vacuum / Water




Connection Tubes

Plastic tubes: PA6, PA11, PA12, Polyethylene, *Polyurethane, PTFE, FEP. *For Polyurethane hoses it is required a minimum hardness of 98 shore.

Applications

- Robotics
- Automotive
- Textile, Packaging, Handling
- Compressed Air Circuit
- Industrial Water
- Vacuum





C Torque specifications





"UNIVERSAL SHORT"


RECOMMENDED TORQUE Nm	BREAKING TORQUE Nm
0,8	3,2
3	8
9	30
10	60
12	50
	0,8 3 9

MEASURE	RECOMMENDED MINIMUM TORQUE Nm	RECOMMENDED MAX TORQUE Nm		
1/8	5	7		
1/4	5	7		
3/8	5	7		
1/2	5	7		

Breaking values may vary according to the item

Breaking values may vary according to the item









Advantages

- 1 The washer is made in stainless steel ensures the perfect tube clamping with every Kinds of materials without damage the surface. The connection between the tube and the fitting ensure a total tightness even in severe conditions such as impact and vibrations.
- 2 The particular geometric shape of the seal ensure the perfect tightness even with vacuum.
- **3** All of threads from this range have been equipped with tightening parts which allow the direct assembly of the fittings, reducing the installation time.
- 4 All the straight fittings can be assembled also with Allen wrench and it is possible to use them in reduced spaces.