

#### **FEATURES**

- Improved low temperature flexibility
- Good abrasion resistance
- Effective kink resistance
- Specially selected high tensile polyester fibres used at the optimum braid angle
- Silicone free

# RS PRO PVC Flexible Tubing, Yellow, 25.5mm External Diameter, 25m Long, Reinforced, Water Applications

RS Stock No.: 197-8285



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Flexible Tubes



#### **Product Description**

This 100% PVC heavy-duty water hose incorporates innovative Spiralap technology for improved longevity and performance in all climatic conditions. An all-year round trusted favourite that retains its flexibility whatever the weather. It is compatible with all leading brands of water hose fittings.

#### **General Specifications**

Material	PVC
Colour	Yellow
Reinforced	Yes
Application	Water, In agriculture for irrigation, Heavy-duty industrial use

#### **Mechanical Specifications**

Inner Diameter	19mm
Outer Diameter	25.5mm
Bend Radius	160mm approx.
Length	25m
Safety Factor	3:1

#### **Operation Environment Specifications**

Minimum Operating Temperature	-15°C
Maximum Operating Temperature	+60°C
Maximum Working Pressure	10 bar

### Flexible Tubes



## Approvals

Compliance/Certifications	BS 3746:1990
---------------------------	--------------