1N4148W



Vishay Semiconductors

Small Signal Fast Switching Diode



DESIGN SUPPORT TOOLS



MECHANICAL DATA

Case: SOD-123 Weight: approx. 10.3 mg

Packaging codes / options:

18/10K per 13" reel (8 mm tape), 10K/box 08/3K per 7" reel (8 mm tape), 15K/box

OLS	click logo to get started
	W

FEATURES

- Silicon epitaxial planar diode
- Fast switching diodes
- AEC-Q101 qualified available
- Base P/N-E3 RoHS-compliant, commercial grade
- Base P/N-HE3 RoHS-compliant, AEC-Q101 qualified
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

PARTS TABLE					
PART	ORDERING CODE	TYPE MARKING	CIRCUIT CONFIGURATION	REMARKS	
1N4148W	1N4148W-E3-08 or 1N4148W-E3-18	A2	Single	Tape and reel	
111414000	1N4148W-HE3-08 or 1N4148W-HE3-18	A2	Single	rape and reel	

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
Reverse voltage		V _R	75	V	
Repetitive peak reverse voltage		V _{RRM}	100	V	
Average rectified current half wave rectification with resistive load $^{\left(1\right)}$	$f \ge 50 Hz$	I _{F(AV)}	150	mA	
Surge forward current	t _p < 1 s	I _{FSM}	500	mA	
Surge forward current	t _p = 1 μs	I _{FSM}	2	А	
Power dissipation ⁽¹⁾		P _{tot}	350	mW	

THERMAL CHARACTERISTICS ($T_{amb} = 25 \degree C$, unless otherwise specified)					
PARAMETER	TEST CONDITION SYMBOL VALU		VALUE	UNIT	
Thermal resistance junction to ambient air ⁽¹⁾		R _{thJA}	357	K/W	
Junction temperature		Тj	150	°C	
Storage temperature range		T _{stg}	-65 to +150	°C	
Operating temperature range		T _{op}	-55 to +150	С°	

Note

⁽¹⁾ Valid provided that electrodes are kept at ambient temperature.

Rev. 1.8, 23-Feb-18

1

RoHS

COMPLIANT

www.vishay.com

Vishay Semiconductors

1N4148W

ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Forward voltage	I _F = 10 mA	VF			1	V
	I _F = 100 mA	V _F			1.2	V
Leakage current	V _R = 20 V	I _R			25	nA
	V _R = 75 V	I _R			5	μA
	V _R = 100 V	I _R			100	μA
	V _R = 20 V, T _J = 150 °C	I _R			50	μA
Diode capacitance	$V_F = V_R = 0 V$	CD			4	pF
Voltage rise when switching ON	Tested with 50 mA pulses, $t_p = 0.1 \ \mu s$, rise time < 30 ns, $f_p = (5 \text{ to } 100) \text{ kHz}$	V _{fr}			2.5	V
Reverse recovery time	$I_F = 10 \text{ mA, } i_R = 1 \text{ mA, } V_R = 6 \text{ V,}$ $R_L = 100 \ \Omega$	t _{rr}			4	ns

TYPICAL CHARACTERISTICS (Tamb = 25 °C, unless otherwise specified)




Fig. 1 - Forward Characteristics




Fig. 2 - Dynamic Forward Resistance vs. Forward Current




Fig. 3 - Admissible Power Dissipation vs. Ambient Temperature




Fig. 4 - Relative Capacitance vs. Reverse Voltage

2

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



Vishay Semiconductors




Fig. 5 - Leakage Current vs. Junction Temperature






Fig. 6 - Admissible Repetitive Peak Forward Current vs. Pulse Duration




Vishay Semiconductors


PACKAGE DIMENSIONS in millimeters (inches): SOD-123







Mounting Pad Layout



Rev. 4 - Date: 24. Sep. 2009 Document no.: S8-V-3910.01-001 (4) ¹⁷⁴³²



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.