





Datasheet Stock No. 184-5569 RS PRO Capacitive Sensor



Specifications:

Mounting: Flush

Rated distance Sn: 5mm(Adjustable) Assured distance Sa: 0...4mm Shape size: 30*50*7mm Output way: NPN

Output status: NO

Supply voltage: 10...30 VDC
Standard target: Fe15*15*1t
Switch point offset[%/Sr]: ≤±20%
Hysteresis range [%/Sr]: 3...20%

Repeated error: ≤3% Load current: ≤200mA Residual voltage: ≤2.5V Current consumption: ≤15mA

Protection circuit: Reverse polarity protection

Output indicator: Yellow LED Ambient temperature:-10℃...55℃ Ambient humidity: 35-95%RH Switch frequency: 60 Hz

High pressure resistance: 1000V/AC 50/60Hz 60s

Insulation resistance: ≥50MΩ(500VDC)

Vibration resistance: Complex amplitude 1.5mm 10...50Hz(2H per X,Y,Z direction)

Protection degree: IP67 Housing material: PBT Connection: 2m PVC cable

Features:

- ◆ Be able to detect both metal and nonmetal objects;
- ◆ Be able to detect various media via nonmetallic container;
- Reliable liquid level detecting;