

PRODUCT-DETAILS

CM-MSS.31S

CM-MSS.31S Therm. motor protec. relay 1n/o+1n/c, 24-240VAC/DC



General Information

| Extended Product Type | CM-MSS.315 |
|-----------------------|---|
| Product ID | 1SVR730712R1400 |
| EAN | 4013614496653 |
| Catalog Description | CM-MSS.31S Therm. motor protec. relay 1n/o+1n/c, 24-240VAC/DC |
| Long Description | The CM-MSS.31S belongs to the CM-MSS thermistor motor protection relay range. It operates with a rated control supply voltage of 24 - 240 V AC / DC and has a 1 n/c + 1 n/o (SPDT) output with contacts rated at 250 V / 4 A. It features one sensor circuit to monitor PTC temperature sensors and works according to the closed-circuit principle. The sensor circuit of the CM-MSS.31S is short-circuit, as well as interrupted-wire monitored and the relay can be reset automatically, manually or remotely after the failure has been removed. This protection relay is certified according to the ATEX directive 94/9/EC and is equipped with a reset / test button. A sealable transparent cover for protection against unauthorized changes is available as accessory. The device offers screw connection technology with double-chamber cage connection terminals |

| Ordering | |
|------------------------|---------------|
| EAN | 4013614496653 |
| Minimum Order Quantity | 1 piece |
| Customs Tariff Number | 85364900 |

| Dimensions | |
|--------------------|---------|
| Product Net Width | 22.5 mm |
| Product Net Height | 85.6 mm |

| Product Net Depth / Length | 103.7 mm |
|-------------------------------|----------|
| Product Net Weight | 0.128 kg |

| Container Information | |
|-----------------------------------|---------------|
| Package Level 1 Units | box 1 piece |
| Package Level 1 Width | 97 mm |
| Package Level 1 Height | 109 mm |
| Package Level 1 Depth / Length | 30 mm |
| Package Level 1 Gross Weight | 0.154 kg |
| Package Level 1 EAN | 4013614496653 |

| Technical | |
|---|--|
| Function | 1 sensor circuit Short-circuit detection Non-volatile fault storage Dynamic interrupted wire detection Auto, manual or remote reset ATEX approved |
| Rated Control Supply Voltage (U _S) | 24 240 V AC/DC |
| Output | 1 n/o + 1 n/c contact |
| Terminal Type | Screw Terminals |
| Rated Operational Current AC-12 (I _e) | (230 V) 4 A |
| Rated Operational Current AC-15 (I _e) | (230 V) 3 A |
| Rated Operational Current DC-12 (I _e) | (24 V) 4 A |
| Rated Operational Current DC-13 (I _e) | (24 V) 2 A |
| Minimum Switching Capacity | 24 V 10 mA |
| Rated Insulation Voltage (U _i) | Measuring Circuit / Output Circuit 300 V Output Circuit 1 / Output Circuit 2 300 V Supply Circuit / Measuring Circuit 300 V Supply Circuit / Output Circuit 300 V |
| Rated Impulse Withstand Voltage (U _{imp}) | Output Circuit 1 / Output Circuit 2 4 kV Output Circuit 4 kV |
| Degree of Protection | Housing IP50 Terminals IP20 |
| Overvoltage Category | |
| Pollution Degree | 3 |
| Short-Circuit Protective Devices | Output Circuit NC - F Type Fuses 10 A Output Circuit NO - F Type Fuses 10 A |
| Electrical Durability | AC-12 100000 cycle |
| Mechanical Durability | 3000000 cycle |
| Connecting Capacity | Flexible 1x 0.5 2.5 mm ² Flexible 2x 0.5 1.5 mm ² Rigid 1x 0.5 4 mm ² Rigid 2x 0.5 2.5 mm ² |
| Tightening Torque | 0.6 0.8 N·m |
| Wire Stripping Length | 8 mm |
| Recommended Screw Driver | Pozidriv 1 4.5 0.8 × 4 |
| Mounting Position | 0.8 X 4 |

| Mounting on DIN Rail | TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 |
|----------------------|--|
| Standards | CAN/CSA C22.2 No.14 |
| | EN 50495 |
| | IEC/EN 63000 |
| | IEC/EN 60079-7 |
| | IEC/EN 60947-5-1 |
| | IEC/EN 60947-8 |
| | UL 508 |
| Environmental | |
| Ambient Air | Operation -25 +60 °C |
| | Storage -40 +85 °C |
| Temperature | |

| Technical UL/CSA | |
|-------------------------------------|--|
| Maximum Operating Voltage UL/CSA | Output Circuit 300 V AC |
| Contact Rating UL/CSA | B300 |
| Connecting Capacity UL/CSA | Flexible 1x 18-14 AWG Flexible 2x 18-16 AWG |
| | Rigid 1x 20-12 AWG |
| | Rigid 2x 20-14 AWG |
| Tightening Torque UL/CSA | 7.08 in lb |

| Certificates and Declarations (Document Number) | |
|---|---|
| ATEX Certificate | EU Type Examination Certificate_TPS_18_ATEX_044254_0018_X |
| CB Certificate | CB_DK-40837-UL |
| CCC Certificate | CCC_2005010303165479 |
| CQC Certificate | CQC2005010303165479 |
| cULus Certificate | cULus508_20140912-E140448 |
| Data Sheet, Technical Information | 2CDC112217D0201 |
| Declaration of Conformity - CCC | 2020980303000194 |
| Declaration of Conformity - CE | 1SVD981007 |
| DNV GL Certificate | DNVGL_TAE00003W4 |
| EAC Certificate | EAC_RU_C-DE.ME77.B.01825 |
| Instructions and Manuals | 1SVC730660M0000 |
| Instructions and Manuals (Part 2) | 1SVC730640M9000 |
| RMRS Certificate | RMRS_1740020250 |
| RoHS Information | 1SVD981007 |

| Classifications | |
|-------------------------------|---|
| Object Classification Code | В |
| ETIM 5 | EC002568 - Temperature monitor (motor protection) |
| ETIM 6 | EC002568 - Relay for thermistor protection (PTC) |
| ETIM 7 | EC002568 - Relay for thermistor protection (PTC) |
| eClass | V11.0 : 27371503 |
| E-Number (Finland) | 2712506 |
| E-Number (Sweden) | 3860728 |

Categories

 ${\sf Low \ Voltage \ Products \ and \ Systems \ \rightarrow \ Control \ Products \ \rightarrow \ Electronic \ Relays \ and \ Controls \ \rightarrow \ Thermistor \ Motor \ Protection \ Relays \ And \ Systems \ \rightarrow \ Control \ Products \ And \ Systems \ \rightarrow \ Control \ Products \ And \ Systems \ \rightarrow \ Control \ Products \ And \ Systems \ Systems \ And \ Systems \ And \ Systems \ Systems \ Systems \ And \ Systems \ And \ Systems \$

