

2-160986-2 ✓ ACTIVE

AMP-TY


TE Internal #: 2-160986-2

Cable Ties, Standard, Bag/Box, 550 Newton Tensile Strength,
123.65 lbf Tensile Strength, Product Length 29.6 in [750 mm]

[View on TE.com >](#)



Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**

Packaging Method: **Bag/Box**

Tensile Strength: **550 Newton**

Product Length: **750 mm [29.6 in]**

Features

Product Type Features

Product Type	Cable Tie
Cable Tie Style	Standard
Tensile Strength	550 Newton

Body Features

Primary Product Color	Black
Primary Product Material	Polyamide 6.6 GF

Dimensions

Bundle Range Diameter	200 mm[7.87 in]
Product Length	750 mm[29.6 in]
Product Width	7.8 mm[.307 in]
Product Thickness	2.07 mm[.081 in]

Packaging Features

Packaging Method	Bag/Box
Packaging Quantity	100

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-T3437-K1
K-Type Tie-On Markers



TE Part # CAT-T3437-Z1
Z-Type Push-On Markers



TE Part # EC4942-000
11310000



TE Part # EC4943-000
11320000



TE Part # EC4941-000
11300000

Documents

[Product Drawings](#)
[CABLE TY 750X7,8BLA](#)



English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2-160986-2_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-160986-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-160986-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

CABLE TIES

English