



Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Cover - Cable Exit**

Cable Exit Angle: **90°**

Strain Relief: **Without**

Primary Product Color: **Black**

Primary Product Material: **PA66**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover - Cable Exit
Sealable	No

Body Features

Cable Exit Angle	90°
Primary Product Color	Black
Primary Product Material	PA66

Mechanical Attachment

Strain Relief	Without
---------------	---------

Dimensions

Compatible Cable Bundle Diameter Range	7.5 mm[.283 in]
--	-----------------

Usage Conditions

Compatible With Connector Style	Housing For Female Terminals, Housing For Male Terminals
Operating Temperature (Max)	120 °C[248 °F]
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]



Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	1000
Packaging Method	Package & Box

Other

Serviceable	Yes
-------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-H3399-CH8172
Heavy Duty Sealed Connector Series Housings

TE Part # 4-967325-1
2,5MM BU-GEH 4P,BL

TE Part # CAT-C4962-CH8172
Circular DIN Housings

Customers Also Bought

TE Part #965783-1
ABDECKAPPE 90GRD

TE Part #2-2205129-3
CA MINI IO TYPE I PIGTAIL

TE Part #213900-2
CPC SEAL ASSY KIT,SRS 6,17-10

TE Part #213902-2
CPC CBL CLMP KIT,LRG,SZ17,BULK

TE Part #1011-333-0205
DT BACKSHELL 90 2way recpt, NV 4.5

TE Part #3-1803055-0
ANVIL, COMBINATION

TE Part #5-1490019-4
CRIMPER, WIRE

TE Part #5-1803171-2
ANVIL

TE Part #7-2151591-7
OCEAN_2.0_SPARE_PART_KIT-063F075F

TE Part #8-1803019-2
CRIMPER, INSULATION O

Documents

Product Drawings

90 DEG CAP CORRUGTD TUBE

English

CAD Files

Customer View Model

ENG_CVM_CVM_185793-1_O.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_185793-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_185793-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[HDSCS Catalog](#)

English

[CONNECTOR SELECTOR](#)

English

Product Specifications

[ADAPTATEURS DE GAINÉ ANNELEE 7,5 MM](#)

English

[Product Specification](#)

English