

## FLAT NOSE PLIERS

DIN ISO 5745 IEC60900

- Flat serrated jaws with wide nose.
- For applications that require wider gripping surface.
- Larger contact area helps grip objects gently to avoid any surface damage or scratches.



Art-No.	LENGTH Inch (mm)	WEIGHT g	TIP WIDTH (mm)	THICKNESS (mm)	HANDLE No.
DFN-6EV	6" (160)	165	10	3	7 11

## DIAGONAL CUTTING PLIERS

DIN ISO 5749 IEC60900

- Forged with Cr-Mo steel. Made to last.
- Cutters are hardened over 58HRC.
- The Cr-Mo steel has higher wear resistance than most common steel used for pliers.
- Ultra smooth precisely riveted joints with no side play.



Art-No.	LENGTH Inch (mm)	WEIGHT g	CAPACITY Ø (mm)	HANDLE No.
DDP-6EV	6" (160)	190	4.0 2.8 2.0	7 11

## WIRE STRIPPING PLIERS

DIN ISO 8979 IEC60900

- Full Copper adjuster for smooth opening adjustment.
- Retaining spring for effortless and efficient action.
- End cutter for stripping cables vertically.



Art-No.	LENGTH Inch (mm)	WEIGHT g	STRIPPING CAPACITY Ø (mm)	HANDLE No.
DWS-6EV	6" (160)	150	10	7 11



## HEAVY DUTY DIAGONAL CUTTING PLIERS

DIN ISO 5749 IEC60900

- Forged with Cr-Mo steel. Made to last.
- The Cr-Mo steel has higher wear resistance than other common steel used for pliers.
- Ultra smooth precisely riveted joints with no side play.



Art-No.	LENGTH Inch (mm)	WEIGHT g	CAPACITY Ø (mm)	HANDLE No.
DDP-7HDV	7" (180)	255	3.8 2.7 2.2	7 11
DDP-8HDV	8" (200)	295	4.2 3.0 2.5	7 11

## WATER PUMP PLIERS

DIN ISO 8976 IEC60900

- Forged with Cr-Mo steel. Made to last.
- Induction hardened jaws up to 58 HRC, high wear-resistance.
- Machined parts with 7 position adjustments.
- Tight grip with lower jaw handle push action, one hand wrenching.
- Pinch proof design.
- Square grooves designed to follow the class circle diameter pipe size (Following adjustment). Rivet department can withstand shocks of up to 180kgs without shedding.



Art-No.	LENGTH Inch (mm)	WEIGHT g	JAW CAPACITY (mm)	ADJUSTMENT	HANDLE No.
DWP-10EV	10" (250)	385	Max. 42	7 position	7 11
DWP-10EDV	10" (250)	385	Max. 42	7 position	7 11



DWP-10EDV: Diamond jaw



Uses unique high frequency hardening process for jaws.

With precision CNC machining.

Max.  
42mm

## CABLE CUTTER

IEC60900

- Forged with Cr-Mo steel. Made to last.
- Precisely treated and sharpened blades, high wear resistance.
- Cr-Mo steel has higher wear resistance than most common steel used for pliers.
- The right tool for cable cutting. Smooth and clean cuts without crushing or deforming the cable.
- For aluminium and copper cable only.



Art-No.	LENGTH Inch (mm)	WEIGHT g	CAPACITY Ø (mm)	HANDLE No.
			 Cable	
DCC-6AV	6" (160)	200	Ø9mm / 22mm²	7 11
DCC-8AV	8" (200)	345	Ø11mm / 38mm²	7 11



Turn 270° as knife



Cutting cable



Stripping cable


## HEAVY DUTY CABLE CUTTER

IEC60900

- Forged with Cr-Mo steel. Made to last.
- Precisely treated and sharpened blades, high wear resistance.
- Cr-Mo steel has higher wear resistance than most common steel used for pliers.
- The right tool for cable cutting. Smooth and clean cuts without crushing or deforming the cable.
- For aluminium and copper cable only.
- Ultra smooth and precisely riveted joints with no side play lasts longer.




Art-No.	LENGTH Inch (mm)	WEIGHT g	CAPACITY Ø (mm)	HANDLE No.
			 Cable	
DCC-10BV	10" (250)	465	Ø13mm / 60mm²	7 11



## 7PCS. TOOL SET



Art-No.	CONTENTS	WEIGHT g
DTS-0701V	DDP-6EV 160mm Diagonal Cutting Pliers DCP-7EV 180mm Combination Pliers DLN-8EV 200mm Long Nose Pliers (-) 3×100mm Screwdriver (+) #0×60mm Screwdriver (-) 4×100mm Screwdriver (+) #1×80mm Screwdriver	970



## 5PCS. TOOL SET



Art-No.	CONTENTS	WEIGHT g
DTS-0501V	DWP-10EDV 250mm Water Pump Pliers DDP-7HDV 180mm Diagonal Cutting Pliers (-) 6.5×150mm Screwdriver (+) #2×100mm Screwdriver (-) 4×100mm Screwdriver	1060

INVISIBLE  
#SPRING  
SERIES



**PATENTED**  
Taiwan:157386  
U.S.A.:6176158 B1  
Australia:711408  
China:01207957,X  
Germany:20105643,7

## COMFORT & SAFETY THROUGH SPRING LOADED ACTION

- Patented invisible spring design provides additional comfort during operation and limits strain on muscles & risks of injuries.
- Special heat-treated steel spring can operate more than 1,000,000 times (lifetime warranty).
- 30% enlarged grip surface adds ergonomic comfort.



## PLUS POINTS


- Patented invisible spring design provides more comfort during operation. User will not feel tired after repeated use. Reduces hand fatigue.
- Made from chrome molybdenum steel. Uses partial high frequency process for cutting edges (over 58 HRC).
- Special heat-treated steel spring can operate more than 1,000,000 times (lifetime warranty).
- Patented two-tone color TPR handles.
- 30% enlarged grip surface provides more handling comfort.

## LABOR SAVING AREA




### Ordinary grips

Less contact area, more labor needed causing more hand fatigue.



### Ergonomic-designed grips

30% more contact with Daiken's grips. Reduces amount of force to be applied.



More than 1,000,000 times



## COMBINATION PLIERS

DIN ISO 5746



- Forged with Cr-Mo steel. Made to last.
- The jaws can grip flat and round objects.

Art-No.	LENGTH Inch (mm)	WEIGHT g	CAPACITY Ø (mm)		HANDLE No.
	L	g	Medium Hard Wire	Hard Wire	
DCP-6EC	6" (160)	225	3.1	2.0	4 10
DCP-7EC	7" (180)	275	3.4	2.2	4 10
DCP-8EC	8" (200)	375	3.8	2.5	4 10






## DIAGONAL CUTTING PLIERS

DIN ISO 5749

- Forged with Cr-Mo steel. Made to last.
- Cr-Mo steel has higher wear resistance than most common steel used for pliers.
- Ultra smooth and precisely riveted joints that last longer. No side play.



Art-No.	LENGTH Inch (mm)	WEIGHT g	CAPACITY Ø (mm)			HANDLE No.
	L	g	Soft Wire	Medium Hard Wire	Hard Wire	
DDP-5EC	5" (125)	145	4.0	2.5	1.8	4 10
DDP-6EC	6" (160)	195	4.0	2.8	2.0	4 10



The front cutting edge is sharper for cutting thin wire. The rear cutting edge is less sharp for cutting thick wire.



## HEAVY DUTY DIAGONAL CUTTING PLIERS

DIN ISO 5749

- Forged with Cr-Mo steel. Made to last.
- Cr-Mo steel has higher wear resistance than most common steel used for pliers.
- Ultra smooth and precisely riveted joints that last longer. No side play.

Art-No.	LENGTH Inch (mm)	WEIGHT g	CAPACITY Ø (mm)			HANDLE No.
	L	g	Medium Hard Wire	Hard Wire	Piano Wire	
DDP-71HEC	7" (180)	280	3.8	2.7	2.2	4 10
DDP-81HEC	8" (200)	300	4.2	3.0	2.5	4 10



## WIRE STRIPPING PLIERS

DIN ISO 8979

- Full Copper adjuster for smooth opening adjustment.
- Retaining spring for more efficient work.
- The end cutter is ideal for stripping cables vertically.



Art-No.	LENGTH Inch (mm)	WEIGHT g	STRIPPING CAPACITY Ø (mm)	HANDLE No.
	L	g	Ø (mm)	
DWS-6EC	6" (160)	170	10	4 10



## TOWER PINCERS

DIN ISO 9242




- Mainly used in construction industry.
- For tie wire cutting and pulling nails.
- Hidden retaining spring, makes the job easier.

Art-No.	LENGTH Inch (mm)	WEIGHT g	CAPACITY Ø (mm)		HANDLE No.
	L	g	Medium Hard Wire	Hard Wire	
DEN-9EC	9" (230)	360	2.4	1.6	PVC Dip
DEN-10EC	10" (250)	380	2.4	1.6	PVC Dip
DEN-11EC	11" (280)	445	2.8	1.8	PVC Dip



## 4-POINT GRIPPING PLIERS

- 45° angled half-round long jaws suitable for gripping spark plugs and round components.






Art-No.	LENGTH Inch (mm)	WEIGHT g	HANDLE No.
			
DMLN-60EU	6" (160)	140	PVC Dip.
DMLN-80EU	8" (200)	215	PVC Dip.



## LONG NOSE PLIERS SERIES

AN  
TYPE

- Hot forged by Cr-Mo. Made to last.
- Mostly used in the automotive and machinery industry.





Art-No.	LENGTH Inch (mm)	WEIGHT g	JAW ANGLE	CROSS SERRATION	HANDLE No.
					
DLN-1100M	11" (275)	310	0°	optional	PVC Dip.
DBN-1145M	11" (275)	310	45°	optional	PVC Dip.
DBN-1190M	11" (275)	310	90°	optional	PVC Dip.
DLN-1600M	16" (400)	410	0°	-	PVC Dip.
DBN-1645M	16" (400)	410	45°	-	PVC Dip.
DBN-1690M	16" (400)	410	90°	-	PVC Dip.



## LONG HOSE PLIERS SERIES

AN  
TYPE





- Mostly used for tubular class aftermarket, spark plugs, wires, pipelines, etc...
- Finely polished. Top workmanship.
- Precise and ultra smooth joint with no side play.
- Finely treated high-strength construction with minimal flex.
- Exceeds ASME standard for professional applications.

Art-No.	LENGTH Inch (mm)	WEIGHT g	JAW Dia. Ø(Inch)	HANDLE No.
				
DLH-11516M	11" (275)	310	5/16"	PVC Dip.
DLH-1112M	11" (275)	310	1/2"	PVC Dip.
DLH-1134M	11" (275)	310	3/4"	PVC Dip.
DLH-16516M	16" (400)	410	5/16"	PVC Dip.
DLH-1612M	16" (400)	410	1/2"	PVC Dip.
DLH-1634M	16" (400)	410	3/4"	PVC Dip.



## OIL FILTER PLIERS





- Mostly used in automotive assembly and disassembly of engine oil filter bottles.

Art-No.	LENGTH Inch (mm)	WEIGHT g	CAPACITY Ø (mm)	HANDLE No.
				
DFW-10P	10" (250)	390	69-80	PVC Dip.
DFW-12P	12" (300)	430	50-114	PVC Dip.



## WIRE ROPE CUTTER

- Ideal for the bicycle industry and professional workshops.
- Well designed cutter angle gives a clean cut section for cables and wire rope.
- Crimp for shifter and brake wire rope.
- Ergonomic handles provide more power output.






Art-No.	LENGTH Inch (mm)	WEIGHT g	CAPACITY Cable Wire Rope	HANDLE No.
				
DWC-7112	7" (180)	280	Steel wrap 1.5	PVC Dip.



## WIRE ROPE CUTTER



- Ideal for the bicycle industry and professional work shops.
- Well designed cutter angle gives a clean cut section for cables and wire rope.
- Crimp for shifter and brake wire rope.
- Ergonomic handles provide more power output.
- Invisible spring system.

Art-No.	LENGTH Inch (mm)	WEIGHT g	CAPACITY Cable Wire Rope	INVISIBLE SPRING	HANDLE No.
					
DWC-20	8" (200)	245	Steel wrap 1.5	✓	20
DWC-21	8" (200)	245	- 1.2	✓	20

