

## Han-Eco 6B-HBM-with SL



Image is for illustration purposes only. Please refer to product description.

Part number	19 43 006 0340
Specification	Han-Eco 6B-HBM-with SL
HARTING eCatalogue	<a href="https://b2b.harting.com/19430060340">https://b2b.harting.com/19430060340</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® B
Type of hood/housing	Bulkhead mounted housing

### Version

Size	6 B
Locking type	Single locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

### Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	RAL 9005 (jet black)
Material (locking)	Polyamide (PA) Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0



Pushing Performance  
Since 1945

## Material properties

Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol Lead
ECHA SCIP number	be45dcda-0f90-459a-a8bc-78fb7986a295
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 61984 EN 45545-2 Fire protection on railway vehicles
CE	Yes

## Commercial data

Packaging size	1
Net weight	96 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140176836
eCl@ss	27440202 Shell for industrial connectors