




Connectors > Circular Connectors > Standard Circular Connectors



Number of Positions: 5

Sealable: No

Connector & Contact Terminates To: **Wire & Cable**

Number of Power Positions: 0

Number of Signal Positions: 5

### Features

#### Product Type Features

Product Type	Connector
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Receptacle

#### Configuration Features

Number of Positions	5
Number of Power Positions	0
Number of Signal Positions	5

#### Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

#### Contact Features

Contact Layout Arrangement	Circular
Circular Connector Contact Type	Socket

#### Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

#### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

#### Packaging Features



Packaging Quantity	1
--------------------	---

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Customers Also Bought



TE Part #6609109-4  
PE0S0DLXC M0=C7031




TE Part #1-796409-1  
CPC PSTD RCPT,23-37,R/A LF



TE Part #5205733-1  
09 PLUG SP/MS STD



TE Part #211769-5  
17-9 CPC RECEPT REV SEX



TE Part #5-102699-9  
20 MODII HDR DRST SHRD A/PIN



TE Part #1-208657-0  
CPC RECEPT ASSEMBLY SIZE 11-8



TE Part #D81438-000  
WP-699191-5-9



TE Part #6-104071-7  
40 SYSTEM 50 HDR SRST SHRD SN

## Documents

### Product Drawings

#### HSG SOC. 5 POS AUDIO MIKE

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_207487-1\\_AC.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_207487-1\\_AC.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_207487-1\\_AC.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

#### Application Specification

English

### Instruction Sheets

#### AMP AUDIO INSTRUMENT CONNECTORS

English

#### Instruction Sheet (U.S.)

English