

# ROLINE U/FTP DataCenter Patch Cord Cat.6A (Class EA), LSOH, slim, white, 1 m

<b>Product No.</b>	21.15.1701
<b>Manufacturer</b>	ROLINE
<b>Manufacturer No.</b>	21.15.1701
<b>EAN (single piece)</b>	7630049610675



**Category 6a twisted-pair patch cable with shielded RJ-45 connectors on both sides. Particularly thin and flexible cable with individual pairs of wires in aluminium-laminated foil for use in confined spaces, such as in data centres.**

- Durable thanks to moulded-on kink protection
- Suitable as patch cable in patch panels or as device connection cable and intended for use in the LAN
- Contact assignment: 1:1 according to EIA/TIA568, 8 cores
- Structure: 8 cores stranded wire, pairs shielded with alu-laminated foil

## Technical specifications

Manufacturer	ROLINE
Product group	Twisted Pair Cable
Product type	FTP Patch Cord
Colour	white
Length	1 m
Shield type	FTP

Transfer quality	Cat6A / Class EA
------------------	------------------

Quantity of wires	8
-------------------	---

Conductor type	Wire
----------------	------

Crossed	No
---------	----

Slim cable	Yes
------------	-----

Colour (Spout)	white
----------------	-------

Cable LSOH	Yes
------------	-----

Side 1 Connector Type	RJ-45
-----------------------	-------

Side 1 Connector Gender	Male
----------------------------	------

Side 2 Connector Type	RJ-45
-----------------------	-------

Side 2 Connector Gender	Male
----------------------------	------

Connector Type RJ45	Standard
---------------------	----------

Operating temperature min.	-10 °C
-------------------------------	--------

Operating temperature max.	60 °C
-------------------------------	-------

Weight	17.4 g
--------	--------

Height of packaging (single piece)	10 mm
---------------------------------------	-------

Width of packaging (single piece)	100 mm
--------------------------------------	--------

Depth of packaging (single piece)	100 mm
--------------------------------------	--------

Package weight (single piece)	0.02 kg
----------------------------------	---------