

FEATURES

- High degree of protection
- Cold impact resistance
- •
- •
- •

RS PRO ATEX Hexagon Screw Plug, Nickel Plated Brass, Without Locknut

RS Stock No.: 2116789, 2116792, 2116788, 2116790, 2116791



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

RS PRO ATEX Hexagon Screw Plug, Nickel Plated Brass, Without Locknut



Product Description

Suitable for use in Zones 1, 2, 21, 22 Equipment group II Devices, machines and apparatus machines and apparatus For mobile applications in offshore and marine industries Chemical and petrochemical industry.

General Specifications

Material:	Nickel-Plated Brass
O-Ring:	Silicone Rubber
Working temperature:	-30 to 80 degree centigrade
Marking:	Ex eb II C Gb/ Ex tD A21 IP68
Protection rating:	IP68

Approvals

Declarations	MFR Declaration of Conformity					
Hazardous Area Certification	ATEX / IECEx					
Standards Met						

RS PRO ATEX Hexagon Screw Plug, Nickel Plated Brass, Without Locknut



Similar Products

RS Aricle No.(will be replaced by new RS ART NO)	Thread Size	Material	GL mm	H mm	W mm	Color	IP Rating	Minimum Operating Temp.	Maximum Operating Temp.	Locknut Included
2116788	M12x1.5	Nickel Plated Brass	5	8	14	Metallic	IP68	-30°C	+80°C	No
2116789	M16x1.5	Nickel Plated Brass	6	9	18	Metallic	IP68	-30°C	+80°C	No
2116790	M20x1.5	Nickel Plated Brass	7	10	22	Metallic	IP68	-30°C	+80°C	No
2116791	M25x1.5	Nickel Plated Brass	7	10	29	Metallic	IP68	-30°C	+80°C	No
2116792	M32x1.5	Nickel Plated Brass	8	11	36	Metallic	IP68	-30°C	+80°C	No

