



## **Data sheet**

# RS PRO Analogue Soldering Station, Auto Sleep, 65W 230V +200°C to +480°C

**Stock number: 202-4512** 

EN



#### **Features:**

- MCU controlled temperature calibration, PID system equipped to ensure temperature stabl and correct.
- Steady temperature setting with 200 ~ 480°C.
- Rapid heating-up, about 1 minute to reach 480°C.

- 65W analogue soldering station easy to control temperature.
- Energy saving with auto sleep function.
- Imported heat-resistant materials heater with long life;
- Easy to replace pluggable heater, reducing consumable replacement cost.
- The heater using low voltage AC source to ensure the anti-static and no leakage, no interference.
- Legerity handle suitable for long time operation.
- Using split design, easy to place.
- Including EU power cord and UK Adaptor.

#### **Specifications:**

Model	2024512			
Power consumption	65W			
Input voltage	230VAC ±10% 50Hz			
Output voltage	24VAC			
Temperature range	200~480°C(392 ~896°F)			
Temperature offset range	±50°C(±90°F)			
Temperature stability	±2°C(still air, no load)			
Temperature accuracy	±10°C			
Temperature adjustment	Rotary knob			
Heater	Pluggable Four core stainless steel heater			
Tip-to-ground impedance	< 2Ω			
Tip-to-ground potential	< 2mV			
Dimensions	L250*W210*H135mm			
Net weight	1.6Kg			

#### **Packing List**

2024512 main unit	1pc
Soldering iron	1pc
Iron holder ( with sponge )	1set
Manual	1сору
Adaptor	1pc

#### EU Plug and UK Adaptor









ptional Soldering Tips:							
SKU	Description	Туре	Size	Tip Length (mm)	Tip Dimensions (mm)		
7998976	Soldering tip, Long Conical,0.008ln/0.2 mm	Straight conical	0.008" (0.2mm)	25mm /0.98ln	R0.2(0.008) 25(0.98)		
7998989	Soldering tip,Single Flat,0.08In/2mm	Straight hoof	0.08" (2mm)	17mm/0.68ln	© 0 17(0.66)		
7998973	Soldering tip,Screwdriver,0.09 4ln/2.4mm	Straight chisel	0.094" (2.4mm)	17mm/0.68In	© 4 0 50 02) 0 50 02) 5 17(0.86)		
7998982	Soldering tip,Screwdriver,0.12 6ln/3.2mm	Straight chisel	0.126" (3.2mm)	17mm/0.68In	© 8 (0.25) (0.5(0.02) (0.55) (0.56)		
7998985	Soldering tip,Screwdriver,0.03 1In/0.8mm	Straight chisel	0.031" (0.8mm)	17mm/0.68In	© © © 0.6(0.024) 17(0.66)		
7998979	Soldering tip,Screwdriver,0.04 7In/1.2mm	Straight chisel	0.047" (1.2mm)	17mm/0.68In	(D) \$ C \ C \ C \ C \ C \ C \ C \ C \ C \ C		
2024516	Soldering tip, Screwdriver,0.06ln/1 .6mm	Straight chisel	0.06" (1.6mm)	17mm/0.68In	© ©   (0.1)   (0.5(0.028)		
2024517	Soldering tip,Single Flat, 0.02ln/0.5mm	Straight hoof	0.02" (0.5mm)	15mm/0.6ln	① (§ 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0		
2024518	Soldering tip,Single Flat, 0.02ln/0.8mm	Straight hoof	0.02" (0.8mm)	17mm/0.66In	(S ∞ 6 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0		
2024520	Soldering tip,Single Flat, 0.04ln/1mm	Straight hoof	0.04" (1mm)	15mm/0.6ln	© (§) 60/15(0.6)		
2024521	Soldering tip, straight conical, 0.008In/0.2mm	Straight conical	0.008" (0.2mm)	17mm/0.64ln	R0.2(0.008)		
2024522	Soldering tip, straight conical, 0.008In/0.2mm	Straight conical	0.008" (0.2mm)	14mm/0.55In	(a)		
2024523	Soldering tip, straight conical, 0.02ln/0.5mm	Straight conical	0.02" (0.5mm)	17mm/0.66ln	R0.5(0.02)		
2024524	Soldering tip, straight knife, 0.02ln/0.5mm	Straight knife	0.02" (0.5mm)	15mm/0.6ln	∯ 15(0.6) 15(0.6)		
2024526	Soldering tip, straight knife, 0.2In/5mm	Straight knife	0.2" (5mm)	15mm/0.6ln	○ ○ ○ ○ ○ ○ ○ ○ ○ ○ ○ ○ ○ ○ ○ ○ ○ ○ ○		
2024527	Soldering tip, straight conical, 0.008In/0.2mm	Straight conical	0.008" (0.2mm)	13mm/0.51ln	(a) (a) (a) (b) (b) (c) (c) (c) (c) (c) (c) (c) (c) (c) (c		
2024528	Soldering tip,Single Flat, 0.1In/3mm	Straight hoof	0.1" (3mm)	17mm/0.66In	(a)		
2024529	Soldering tip,Single Flat, 0.16ln/4mm	Straight hoof	0.16" (4mm)	17mm/0.66In	(a) (a) (b) (a) (a) (a) (a) (a) (a) (a) (a) (a) (a		
2024530	Soldering tip, bent conical, 0.008In/0.2mm	Bent conical	0.008" (0.2mm)	12mm/0.47ln	(So) 12.0		
2024532	Soldering tip, straight knife, 0.08ln/2mm	Straight knife	0.08" (2mm)	14mm/0.55In	2 14		
2024533	Soldering tip, bent conical, 0.02ln/0.5mm	Bent conical	0.02" (0.5mm)	18.3mm/0.72In	(153)		

### Optional Soldering Iron:

SKU	202-4513		
Description	RS PRO Soldering Iron for		
Picture	No. of the latest state of		