

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2177971021](#)
Status: **Active**
Overview: [Off-the-Shelf Cable Assemblies](#)
Description: KK 254-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.54mm Pitch, Single Row, 150.00mm Length, 2 Circuits, Natural

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	217797
Assembly Configuration	Dual Ended Connectors
Connector to Connector	KK 254-to-Pigtail
Overview	Off-the-Shelf Cable Assemblies
Product Name	KK 254
Type	Discrete Wire Assembly
UPC	195842122987

Physical

Cable Length	150.00mm
Circuits (Loaded)	2
Color - Resin	Natural (White)
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.738/g
Number of Rows	1
Pitch - Mating Interface	2.54mm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.57mm max.
Wire Size AWG	22
Wire/Cable Type	UL 11028

Material Info

Reference - Drawing Numbers

Sales Drawing	2177971021-000
---------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Benzo(ghi)perylene
Octanoic acid,
2,2,3,3,4,4,5,5,6,6,7,7,8,8,8-
pen
Dodecamethylcyclhexasiloxane
Decamethylcyclpentasiloxane
Octamethylcycltetrasiloxane
Disodium 3,3'-[[1,1'-
Biphenyl]-4,4'-
Diylbis(Azo)
1,2-
Benzenedicarboxylic
acid, bis(3-
methylbutyl)
1,2-diethoxyethane
Dibutyltin-dichloride
C.I. Direct Black 38
Ammonium-
pentadecafluorooctanoate
Phenol, 2-(2H-
benzotriazol-2-yl)-4,6-
bis(1,1-dim
2-ethylhexyl 10-
ethyl-4,4-dioctyl-7-
oxo-8-oxa-3,
Dibutylbis(pentane-2,4-
dionato-O,O')tin
2-(2H-Benzotriazol-2-
yl)-4,6-
ditertpentylphenol
2-(2H-Benzotriazol-2-
yl)-4-(tert-butyl)-6-
(sec-b
1,2-
Benzenedicarboxylic

China RoHS

acid, dihexyl ester,
bra
diisohexyl phthalate
1,2-
Benzenedicarboxylic
acid, dipentyl ester, br
Zirconia
Aluminosilicate
Refractory Ceramic
Fibr
Nonadecafluorodecanoic
acid (PFDA) and its
sodiu
Tris(4-nonylphenyl,
branched and linear)
phosphi
Perfluorobutane
sulfonic acid (PFBS)
and its sal
Fluoranthene
Pyrene
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o
Dioctyltin dilaurate,
stannane, dioctyl-,
bis(co
Perfluorononan-1-
oic acid
(2,2,3,3,4,4,5,5,6,6,7
Perfluorohexane-1-
sulphonic acid and its
salts
Dipentyl phthalate
Cobalt-dichloride
Alkanes, C10-13,
chloro
Bis(tributyltin) oxide
Lead chromate
Lead chromate
molybdate sulfate red
Tris(2-chloroethyl)
phosphate
bis(2-methoxyethyl)
ether
1,2-Dimethoxyethane
1,2-bis(2-
methoxyethoxy)ethane
Decabromodiphenylether
Diboron-trioxide
Cadmium-oxide
Lead(II,IV)-oxide
Lead
Cadmium
Lead-dinitrate
Lead-titanium-trioxide
Pentalead-tetraoxide-
sulphate
Tetralead-trioxide-
sulphate
Dioxobis(stearato)trilead
Lead titanium
zirconium oxide
Cyanamide, lead(2+)
salt (1:1)
Sulfurous Acid, Lead
Salt, Dibasic

Silicic acid (H₂Si₂O₅),
barium salt (1:1),
lead-
[Phthalato(2-)]dioxotrilead
4-aminoazobenzene
N,N-
Dimethylformamide
Phenanthrene
Imidazolidine-2-thione

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[217797](#) Series

Mates With

KK254 PCB Headers
 [42375](#) , [42377](#)
, [42376](#) , [4030](#) , [6373](#) , [6410](#) , [1718](#) 56,
[171857](#)

This document was generated on 08/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION