

FEATURES

Rapid detection function

Precise non-contact measurements

Circular laser sighting

Unique flat surface, modern housing design

Automatic Data Hold

Emissivity Digitally adjustable from 0.10 to 1.0

MAX, MIN, AVG, DIF temperature displays

Backlight LCD display

Automatic selection range and Display Resolution 0.1°C(0.1°F)

Set high and low alarms with red backlight

Type-k input

RS PRO Infrared Thermometer

RS Stock No.: 206-8744



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This is capable of non-contact (infrared) temperature measurements at the touch of a button. The built-in laser pointer increases target accuracy while the backlight LCD and handy push-buttons combine for convenient, ergonomic operation. The non-contact Infrared Thermometers can be used to measure the temperature of objects' surface that is improper to be measured by traditional (contact) thermometer (such as moving object, the surface with electricity current or the objects which are uneasy to be touched.)

Proper use and care of this meter will provide years of reliable service.

General Specifications

Model Number	RS-8876
Temperature Range	-50 to 1000°C (-58°F ~ 1832°F)
	-50 ~ 20°C (-58°F ~ 68°F) ±3.5°C (6.3°F)
Best Accuracy	20°C ~300°C (68°F ~572°F) ±1.0% ±1.0°C (1.8°F)
	300°C ~1000°C (572°F ~ 1832°F) ±1.5%
Display Type	LCD with a backlit
Distance to Spot Ratio	20:1
Response Time	150ms
Spectral response	8 to 14 um
Emissivity	Digitally adjustable from 0.10 to 1.0
Display resolution	0.1°C (0.2°F)
Repeatability (% of reading)	-50~20°C (-31~68°F): ±1.8°C (3.2°F)
	20~1000°C (68~1832°F): ±0.5% or ±0.5°C (0.9°F)
Hold Temperature Reading	7to 10 Seconds
Temperature Scale	Both
Auto Capture	
Flashlight	Yes
Low Battery Indication	Yes
Over range indication	Yes
Auto Power Off	Yes
Internal memory	
Applications	
Calibration Availability	

Infrared Thermometer

Electrical Specifications

Battery Included Yes

Battery Type 9V

Battery Life

Mechanical Specifications

Dimensions 190X55X110 mm

Length 190mm

Width 55mm

Height 110mm

Weight 263g

Environmental Specifications

Drop Test

Operating temperature 0 to 50° C (32 to 122° F)

Storage temperature - 10 to 60° C (14 to 140° F)

Operating humidity 10%~90%RH operating, <80%RH storage

Operating altitude 2000 meters above mean sea level

Protection Category

IP Protection IP54

Laser safety IEC 60825-1 Class 2, 630-670 nm, < 1 mW

Additional Information

EAN

Custom Tariff Number 9025191000

Approvals

Compliance/Certifications CE

Declarations

Hazardous Area Certification