

FEATURES

- Non-latching and latching versions which are guarded
- full actuator travel
- Screw terminals and self-lifting clamp for connection of leads
- Sealed to IP67
- Operating Temperature: -25°C to 60°C
- Ergonomic design
- Yellow colour protective guard with a black base
- Metal guard provides extra safety

RS PRO Momentary Heavy Duty Foot Switch - Die Cast Aluminium Case Material, NC/NO, 3 A @ 500 V ac Contact Current, 230V

RS Stock No.: 211-0711



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description ATTRIBUTE 1

RS PRO rugged heavy duty guarded foot switches which are ideal for industrial applications. The protective guard provides extra user safety and stops the machine from accidentally starting. The guards are large enough for safety shoes to be worn when using the foot switches.

This range of heavy duty foot pedal switches includes:

208-3265 - Momentary Staggered, Single Switch With Double Action Contacts

<u>211-0711</u> – Momentary Single Non-latching Switch

<u>228-2103</u> - Momentary Double Pole Double Throw (DPDT)

440-5566 - Momentary Single Pole Single Throw (SPST)

771-9243 - Momentary Double Pole Double Throw (DPDT)

841-772 - Latching 1NO 1NC

General Specifications

| Contact Configuration | NC/NO |
|-----------------------|---|
| Switch Operation | Momentary |
| Case Material | Die Cast Aluminium |
| Switch Environment | Heavy Duty |
| Contact Material | Silver |
| Guard Cover | Yes |
| Colour | Yellow |
| Applications | Foot switches are commonly used in applications where hands-free control is more practical or safer. They can be found on: Industrial machinery and smaller power tools, Hospital beds, Dentist Chairs, Lamps |

Electrical Specifications

| Contact Voltage Rating (AC) | 230V |
|-----------------------------|---------------|
| Contact Voltage Rating (DC) | 24V |
| Contact Current Rating | 3A @ 500 V ac |

Foot Switches



Mechanical Specifications

| Length | 264mm |
|-------------|--------------------------|
| Height | 155mm |
| Dimensions | 264mm x 163mm x 155mm |
| Width | 163mm |
| Contact Gap | <3mm, Suitable for Mains |

| Operation Environment Specifications | |
|--------------------------------------|---------------|
| Operating Temperature | -25°C to 60°C |

| Protection Category | |
|---------------------|------|
| IP Rating | IP67 |

| Approvals | |
|---------------------------|---|
| Standards Met | EN 60204-1, EN 60947-5-1, IEC 947-5-1, VDE 0660 Part 200 |
| Compliance/Certifications | EN 60204-1/EN60947-5-1, RoHS |



Foot Switches





Outline Dimensions

