

ROLINE Fibre Optic Jumper Cable, 50/125 µm, LC/LC, OM5, green, 7 m

Product No.	21.15.9276
Manufacturer	ROLINE
Manufacturer No.	21.15.9276
EAN (single piece)	7630049620087



LSOH

ROLINE fiber optic patch cables in OM5 quality for high-performance fiber optic cabling in high-density environments.

- Security for the future! The OM5 fiber connector quality with very low insertion ensures an excellent quality at very high bandwidths of up to 100 Gbit/s Ethernet, Fibre Channel, and OIF applications with up to 150 meters - extends the system cost benefits to ultra long building backbones and medium length campus backbones.
- Material and clothing in ROLINE quality
- Duplex cables with fiber type Multimode 50/125µm, OM5
- Attenuation 850nm ≤ 2.3 dB/km, 953nm ≤ 1.7 dB/km, 1300nm ≤ 0.6 dB/km
- The cable assembled with "low-loss" connectors achieve very good values for insertion loss and reflection. Insertion loss of less than 0.3dB
- Outer diameter: 2.0mm
- UPC polish
- Modal Bandwidth: 4700 MHz-km (this bandwidth is based on application-specific implementation of the EMBC requirements)

Technical specifications

Manufacturer	ROLINE
--------------	--------

Product group	Fibre optic cable
Product type	Fibre Optic Jumper Cables OM5
Colour	green
Length	7 m
Quantity of fibre	2
Conductor composition	Compact conductor
Cable type	Duplex Cable
External cable	No
Fibre section	50/125µm OM5
Connection ports	LC / LC
Side 1 Connector Type	LC
Side 2 Connector Type	LC
Aramid strain relief	Yes
External cable diameter	2 mm
Mantle of external cable	PVC
Cable LSOH	Yes
Weight	53.4 g
Height of packaging (single piece)	20 mm
Width of packaging (single piece)	100 mm
Depth of packaging (single piece)	100 mm
Package weight (single piece)	0.02 kg