

Vishay BCcomponents


30 V to 60 V PTC Thermistors For Overload Protection





QUICK REFERENCE DATA				
PARAMETER	VALUE	UNIT		
Maximum voltage (DC or AC)	30 to 60	V		
Holding current	0.094 to 2	Α		
Resistance at 25 °C (R ₂₅)	0.3 to 50	Ω		
I _{max.}	0.8 to 23	Α		
Switch temperature	140	°C		
Operating temperature range at max. voltage	- 40 to + 85	°C		
Climatic category	40/125/56			

FEATURES





• Small ratio between trip and non-trip currents ($I_t/I_{nt} = 1.5$ at 25 °C)

RoHS

- High maximum overload current (up to 23 A)
- Leaded parts withstand mechanical stresses and vibration
- UL file E148885 according to XGPU standard UL1434
- UL approved PTCs are guaranteed to withstand severe test programs
 - Long-life cycle tests (over 5000 trip cycles)
 - Long-life storage tests (3000 h at 250 °C)
 - Electrical cycle tests at low ambient temperatures (- 40 °C or 0 °C)
 - Damp-heat and water immersion tests
 - Overvoltage tests at up to 200 % of rated voltage
- Compliant to RoHS directive 2002/95/EC and in accordance to WEEE 2002/96/EC

APPLICATIONS

Over-temperature/over-load protection:

- Telecommunications
- · Automotive systems
- Industrial electronics
- · Consumer electronics
- Electronic data processing

DESCRIPTION

These directly heated thermistors have a positive temperature coefficient and are primarily intended for overload protection. They consist of a naked disk with two tinned brass or copper clad steel leads and are coated with a high temperature silicone UL 94 V-0 coating. Leadless disks and leaded disks without coating are available on request.

MOUNTING

The PTC Thermistors are suitable for processing on automatic insertion equipment.

Typical soldering

235 °C; duration: 5 s (Pb-bearing) 245 °C, duration: 5 s (Lead (Pb)-free)

Resistance to soldering heat 260 °C. duration: 10 s max.

MARKING

Only the grey lacquered thermistors with a diameter of 8.5 mm to 20.5 mm are marked with BC, R_{25} value (example 1R9) on one side and $I_{\rm nt}$, $V_{\rm max.}$ on the other side.

2381 66. 5...1/PTCCL..H....BE

Vishay BCcomponents

30 V to 60 V PTC Thermistors For Overload Protection



ELECTRICAL DATA AND ORDERING INFORMATION for 2381 66. 51; max. voltage = 30 V to 60 V (AC or DC) (1)									
Int MAX.	I _t MIN.	R ₂₅	V	I MAX. (2)	I _{res} MAX.	DISSIP.	ØD	CATALOG NUMBERS	
at 25 °C (mA)	at 25 °C (mA)	± 20 % (Ω)	MAX. (V)	at 25 °C (mA)	at V _{max.} and 25 °C (mA)	FACTOR (mW/K)	MAX. (mm)	BULK	TAPE ON REEL
94	145	50	60	800	22	6.9	5	2381 660 59491	2381 660 69491
130	195	25	60	1200	25	6.9	5	2381 660 51311	2381 660 61311
180	270	13	30	1700	45	6.9	5	2381 660 51811	2381 660 61811
270	405	6	30	2500	60	6.9	5	2381 660 52711	2381 660 62711
320	480	5	30	3500	62	7.8	7	2381 661 53211	2381 661 63211
410	615	3	30	4500	65	7.8	7	2381 661 54111	2381 661 64111
470	705	2.5	30	5000	70	8.8	8.5	2381 661 54711	2322 661 64711
540	810	1.9	30	6000	75	8.8	8.5	2381 661 55411	2381 661 65411
610	915	1.7	30	7000	80	9.9	10.5	2381 662 56111	2381 662 66111
700	1050	1.3	30	8000	90	9.9	10.5	2381 662 57011	2381 662 67011
830	1245	1.1	30	10 000	100	11.5	12.5	2381 662 58311	2381 662 68311
920	1380	0.9	30	11 000	105	11.5	12.5	2381 662 59211	2381 662 69211
1170	1755	0.7	30	13 500	140	14.5	16.5	2381 663 51121	-
1390	2085	0.5	30	16 000	170	14.5	16.5	2381 663 51321	-
1770	2655	0.4	30	20 000	200	18.7	20.5	2381 664 51721	=
2050	3075	0.3	30	23 000	220	18.7	20.5	2381 664 52021	-

Notes


 $I_{max.}$ is the maximum overload current that may flow through the PTC when it passes from the low ohmic to the high ohmic state. UL approval: $I_{max.}$ x 0.85

SAP AND 12NC PART NUMBERS					
12NC	SAP CODING	12NC	SAP CODING		
2381 660 x9491	PTCCL05H940EyE	2381 662 x6111	PTCCL11H611DyE		
2381 660 x1311	PTCCL05H131EyE	2381 662 x7011	PTCCL11H701DyE		
2381 660 x1811	PTCCL05H181DyE	2381 662 x8311	PTCCL13H831DyE		
2381 660 x2711	PTCCL05H271DyE	2381 662 x9211	PTCCL13H921DyE		
2381 661 x3211	PTCCL07H321DyE	2381 663 51121	PTCCL17H112DBE		
2381 661 x4111	PTCCL07H411DyE	2381 663 51321	PTCCL17H132DBE		
2381 661 x4711	PTCCL09H471DyE	2381 664 51721	PTCCL21H172DBE		
2381 661 x5411	PTCCL09H541DyE	2381 664 52021	PTCCL21H202DBE		

Notes

- For bulk parts replace x by "5" and y by "B"
- For taped on reel parts replace it x by "6" and y by "T"

CURRENT DEVIATION AS A FUNCTION OF THE AMBIENT TEMPERATURE




For technical questions, contact: nlr@vishay.com
Document Number: 29085
Revision: 29-Jul-09

⁽¹⁾ The thermistors are clamped at the seating plane.




30 V to 60 V PTC Thermistors For Overload Protection Vishay BCcomponents

VOLTAGE DERATING AS A FUNCTION OF AMBIENT TEMPERATURE




ELECTRICAL CHARACTERISTICS Imax. AS A FUNCTION OF VOLTAGE



 $I_{\text{max.}}$ as stated in the electrical data and ordering information tables, is the maximum overload current that may flow through the PTC when passing from the low ohmic to high ohmic state at rated voltage.

When other voltages are present after tripping, the $I_{max.}$ value can be derived from the above $I_{max.}$ as a function of voltage graph. Voltages below V_{rated} will allow higher overload currents to pass the PTC.

TYPICAL TRIP-TIME AS A FUNCTION OF TRIP CURRENT RATIO



Curve 1: \emptyset D_{max.} = 20.5 mm Curve 2: \emptyset D_{max.} = 16.5 mm

Curve 3: \emptyset D_{max.} = 12.5 mm Curve 4: \emptyset D_{max.} = 10.5 mm

Curve 5: Ø D_{max.} = 8.5 mm

Curve 6: \emptyset D_{max.} = 7.0 mm

Curve 7: \emptyset D_{max.} = 5.0 mm Measured in accordance

Measured in accordance with "IEC 60738".

Trip-time or switching time (t_s)

To check the trip-time for a specific PTC, refer to the Electrical Data and Ordering Information tables for the value I_{nt} . Divide the overload or trip current by this I_{nt} and you realize the factor I_t/I_{nt} . This rule is valid for any ambient temperature between 0 °C and 70 °C. Adapt the correct non-trip current with the appropriate curve in the Current Deviation as a Function of the Ambient Temperature graph. The relationship between the I_t/I_{nt} factor and the switching time is a function of the PTC diameter; see the above graphs.

Example

What will be the trip-time at $I_{ol} = 3$ A and $T_{amb} = 0$ °C of a thermistor type 2381 661 54711; 2.5 Ω ; Ø $D_{max} = 8.5$ mm:

Int from the table: 470 mA at 25 °C

 I_{nt} : 470 x 1.12 = 526 mA (at 0 °C).

Overload current = 3 A; factor I_t/I_{nt} : $^3/_{0.526}$ = 5.70. In the typical trip-time as a function of trip current ratio graph, at the 8.5 mm line and I_t/I_{nt} = 5.70, the typical trip-time is 1.7 s.

Document Number: 29085 Revision: 29-Jul-09


Vishay BCcomponents

30 V to 60 V PTC Thermistors For Overload Protection




COMPONENTS OUTLINE				
CODE NUMBER 2381		SPQ	OUTLINE	
660	51	500	Fig. 1a	
	61	1500	Fig. 1b	
661	51	250	Fig. 1a	
	61	1500	Fig. 1b	
	51	250	Fig. 1a	
662	66111 to 67011	1500	Fig. 1b	
	68311 to 69211	750	Fig. 1b	
663	51	200	Fig. 1a	
664	51	100	Fig. 1a	

PTC THERMISTORS IN BULK



DIMENSIONS OF BULK TYPE PTC'S (in mm				
D	See table			
d	0.6 ± 10 %			
Т	4.0 max.			
H2	4.0 ± 1.0			
НЗ	D + 5 max.			
L1	20 min.			
F	5.0			

PTC THERMISTORS ON TAPE ON REEL



TAPE AND REEL ACCORDING TO IEC 60286-2 dimensions in millimeters					
SYMBOL	PARAMETER	TOLERANCE			
D	Body diameter	See table	max.		
d	Lead diameter	0.6	± 10 %		
Р	Pitch of components Diameter < 12 mm Diameter ≥ 12 mm	12.7 25.4	± 1.0 ± 2.0		
P ₀	Feedhole pitch	12.7	± 0.3		
F	Leadcenter to leadcenter distance (between component and tape)	5.0	+ 0.6 - 0.1		
H0	Lead wire clinch height	16.0	± 0.5		
H2	Component bottom to seating plane	4.0	± 1.0		
НЗ	Component top to seating plane	D + 5	max.		
Т	Total thinkness	4.0	max.		


www.vishay.com 18 For technical questions, contact: nlr@vishay.com

Document Number: 29085 Revision: 29-Jul-09




30 V to 60 V PTC Thermistors For Overload Protection Vishay BCcomponents


TYPICAL RESISTANCE/TEMPERATURE CHARACTERISTIC




TYPICAL RESISTANCE/TEMPERATURE CHARACTERISTIC



TYPICAL RESISTANCE/TEMPERATURE CHARACTERISTIC



TYPICAL RESISTANCE/TEMPERATURE CHARACTERISTIC



Document Number: 29085 Revision: 29-Jul-09



Vishay

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Revision: 18-Jul-08

Document Number: 91000 www.vishay.com