

FEATURES

- Integral foot plate provides secure, fast mounting.
- Spigot designed for speedy installation of flexible ducting.
- 3 Speed fan setting
- Mixed flow fans develop greater pressure than conventional axial fans making them ideal for use in ducted systems.
- IPX4 rated CE marked in accordance with all the relevant EEC Harmonised Directives.

RS PRO Mixed Flow Extraction Fans

RS Stock No.: 2192980, 2192981



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

100mm mixed flow high performance extract fan range suitable for use in restricted spaces such as ceiling restricted spaces such as ceiling voids traditionally found in refurbishments.

General Specifications

Fully Building Code Compliant	
Height	180mm
Width	168mm
Depth	298mm

Mechanical Specifications

Double Insulated with motor fitted with Thermal Protection

Electrical Specifications

High Speed	245m ³ /h
Low Speed	180m ³ /h
Rated Voltage	220-240v-50Hz
High Rated Wattage	25W
Low Rated Wattage	20W
High Speed Noise Level	24dB(A) @ 3m
Low Speed Noise Level	20dB(A) @ 3m



Extractor Fans

Approvals

Declarations	MFR Declaration of Conformity