


PCB - BC 107,6/40 U11 HBUS DEV-PCB - 2202544

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Printed-circuit board for the BC 107,6 DEV-KIT




Why buy this product

- Hole matrix PCB for self-assembly
- Assembly area approx. 7,650 mm²
- Hole matrix dimension: 2.54 mm



Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 142418
GTIN	4055626142418
Weight per Piece (excluding packing)	32.500 g
Custom tariff number	85340011
Country of origin	Germany

Technical data

General

Housing type	Component housing
Housing material	FR 4-21
Color	green

Ambient conditions

Ambient temperature (operation)	110 °C (depending on power dissipation)
---------------------------------	---

Dimensions

Pitch	2.54 mm
	5 mm

Technical data

PCB - BC 107,6/40 U11 HBUS DEV-PCB - 2202544

Technical data

Technical data

Flammability rating according to UL 94	V0
--	----

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Accessories

Additional products

Electronic housing - BC 107,6 DEV-KIT KMGY - 2202525



DEV-KIT BC 107,6: contains 1 x BC 107,6 housing and PCB terminal blocks (MKDS), supplied in individual parts

Plug - HBUS 107,6-16P-1S DEV-KIT BK - 2202545

Bus connector to connect BC modules on the DIN rail; suitable for BC DEV-KITS, contains HBUS 107,6 and pin strip

