


DATASHEET

SMD • B 23-23B/R6GHBHC-A01/2A



Features

- Package in 8mm tape on 7" diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Mono-color type.
- Pb-free.
- The product itself will remain within RoHS compliant version.

Description

- The 23-23B SMD LED is much smaller than lead frame type components, thus enable smaller board ize, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

Applications

- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.



Device Selection Guide

Chip Type	Chip Materials	Emitted Color	Resin Color
R6	AlGaInP	Brilliant Red	
GH	InGaN	Brilliant Green	Water Clear
ВН	InGaN	Blue	

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit		
Reverse Voltage	V_R	5	V		
Forward Current	I _F	R6 : 25 GH : 20 BH: 20	mA		
Peak Forward Current (Duty 1/10 @1KHz)	I _{FP}	R6 : 60 GH : 75 BH: 75	mA		
Power Dissipation	Pd	R6 : 60 GH : 95 BH: 95	mW		
Operating Temperature	T _{opr}	-40 ~ +85	$^{\circ}\mathbb{C}$		
Storage Temperature	Tstg	-40 ~ +90	$^{\circ}\mathbb{C}$		
Electrostatic Discharge	ESD _{HBM}	R6 : 2000 GH : 150 BH: 150	V		
Soldering Temperature	T _{sol}	Reflow Solderi Hand Solderin	Reflow Soldering : 260 °C for 10 sec. Hand Soldering : 350 °C for 3 sec.		

Electro-Optical Characteristics (Ta=25℃)


Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Luminaua Internitu	1	R6: 72	100			I 00 A
Luminous Intensity	lv	GH: 140 BH: 45	200 65		mcd	$I_F = 20 \text{mA}$
Viewing Angle	2θ _{1/2}		130		deg	I _F =20mA
		R6:	632			
Peak Wavelength	λр	GH :	518		nm	$I_F = 20 \text{mA}$
		BH:	468			
Danis (Manaland)	.	R6:	624			I 00 A
Dominant Wavelength	λd	GH :	525		nm	$I_F = 20 \text{mA}$
		BH:	470			
		R6:	20			
Spectrum Radiation Bandwidth	$\triangle \lambda$	GH :	35		nm	$I_F = 20 \text{mA}$
		BH:	25			
		R6:1.7	2.0	2.4		
Forward Voltage	V_F	GH: 2.7	3.3	3.7	V	$I_F = 20 \text{mA}$
		BH: 2.7	3.3	3.7		
		R6:		10		
Reverse Current	I_R	GH :		50	μA	$V_R = 5V$
		BH:		50		


Note:


Tolerance of Luminous Intensity: ±11%





Typical Electro-Optical Characteristics Curves R6

















Rev.6





Typical Electro-Optical Characteristics Curves GH





















Typical Electro-Optical Characteristics Curves BH















Package Outline Dimensions




Suggested pad dimension is just for reference only. Please modify the pad dimension based on individual need.

Note: Tolerances unless mentioned ±0.1mm. Unit = mm




Moisture Resistant Packing Materials Label Explanation



- · CPN: Customer's Product Number
- P/N: Product Number
- QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- HUE: Chromaticity Coordinates & Dom. Wavelength Rank
- REF: Forward Voltage Rank
- · LOT No: Lot Number


Reel Dimensions



Note: The tolerances unless mentioned is ± 0.1 mm ,Unit = mm




Carrier Tape Dimensions: Loaded quantity 2000 PCS per reel



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

Moisture Resistant Packaging





Precautions For Use

1. Over-current-proof


Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

- Storage
- 2.1 Do not open moisture proof bag before the products are ready to use.
- 2.2 Before opening the package: The LEDs should be kept at 30℃ or less and 90%RH or less.
- 2.3 After opening the package: The LED's floor life is 1 year under 30°C or less and 60% RH or less.

If unused LEDs remain, it should be stored in moisture proof packages.

2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions. Baking treatment: $60\pm5^{\circ}$ C for 24 hours.

- 3. Soldering Condition
- 3.1 Pb-free solder temperature profile




- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350°C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.





Application Restrictions

High reliability applications such as military/aerospace, automotive safety/security systems, and medical equipment may require different product. If you have any concerns, please contact Everlight before using this product in your application. This specification guarantees the quality and performance of the product as an individual component. Do not use this product beyond the specification described in this document.