





## **Model Number**

#### UC400-F77-IU-IO-V31


Single head system

#### **Features**

- **IO-Link interface for** parameterization
- Programmable via DTM with **PACTWARE**
- Selectable sound lobe width
- Synchronization options
- **Temperature compensation**
- **Analog output**

## **Diagrams**


### Characteristic response curve





Date of issue: 2017-10-27

Release date: 2017-10-24 11:48



# **Technical data**

General specifications	
Sensing range	30 400 mm
Adjustment range	40 400 mm
Dead band	0 30 mm
Standard target plate	20 mm x 20 mm
Transducer frequency	approx. 310 kHz
Response delay	minimum : 10 ms factory setting: 37 ms

≥ 10 ms (factory setting); Sensor cycle time programmable to 60 s

Non-volatile memory **EEPROM** Write cycles 300000

Indicators/operating means LED green solid: Power on

flashing: Standby mode or IO-Link communication LED yellow solid: object in evaluation range flashing: programming of the limits, object detected

LED red solid: fault Flashing: programming limits, object not detected

**Electrical specifications** 

18 ... 30 V DC , ripple 10 %SS Operating voltage UB

No-load supply current I<sub>0</sub> ≤ 50 mA Power consumption P<sub>0</sub>  $\leq$  500 mW Time delay before availability tv < 300 ms

Interface Interface type

Memory

IO-Link (after individual activation via programming button Input/Output

Input/output type 1 synchronization connection, bidirectional 0 Level 0 ... 1 V 2.5 V ... U<sub>B</sub> 1 Level Input impedance  $> 22 k\Omega$ 

Output rated operating current current source < 2.5 mA

≥ 1 ms with external control, low active Pulse length

Synchronization frequency Common mode operation < 109 Hz

Multiplex operation  $\leq 109~Hz~/~n$  , n = number of sensors ,  $n \leq 10$ 

Output

Output type 1 analog output 0 (4) ... 20 mA or 1 analog output 0 ... 10 V

Resolution current output: evaluation range [mm]/3200 but ≥ 0.35 mm

voltage output: evaluation range [mm]/4000 but  $\geq$  0.35 mm

Deviation of the characteristic curve ≤±1 % of full-scale value ≤ ± 0.1 % of full-scale value Repeat accuracy current output: ≤ 500 Ohm Load impedance voltage output: ≥ 1000 Ohm

Temperature influence  $\leq \pm 0.75$  % of the end value (with temperature compensation)

from 10 minutes after switching on the sensor; 0,17 %/K

(without temperature compensation)

**Ambient conditions** current output -25 ... 60 °C (-13 ... 140 °F) voltage output -25 Ambient temperature

... 70 °C (-13 ... 158 °F) -40 ... 85 °C (-40 ... 185 °F) Storage temperature

Mechanical specifications

Connection type Connector plug M8 x 1, 4-pin Degree of protection IP67

Material

Housing Polycarbonate

Transducer epoxy resin/hollow glass sphere mixture; polyurethane foam

Installation position any position

9 g

Tightening torque, fastening screws max. 0.2 Nm

**Factory settings** 

Output near limit: 40 mm far limit: 400 mm Output mode: rising ramp output type: 4 ... 20 mA

Beam width wide

Compliance with standards and

directives Standard conformity

Standards EN 60947-5-2:2007+A1:2012

IEC 60947-5-2:2007 + A1:2012


EN 60947-5-7:2003 IEC 60947-5-7:2003

Approvals and certificates


**UL** approval cULus Listed, Class 2 Power Source

CCC approval CCC approval / marking not required for products rated ≤36 V

## **Dimensions**



## **Electrical Connection**



\*if not used connect to ground (0V)

## **Pinout**




Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

## **Additional Information**

## Analog output modes



FPEPPERL+FUCHS

#### **Accessories**

### IO-Link-Master02-USB

IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection

#### V31-GM-2M-PVC

Female cordset, M8, 4-pin, PVC cable

#### V31-GM-1M-PVC-V1-G

Double-ended cordset, M8 to M12

#### OMH-ML7-01

Mounting aid for ML7 and ML8 series, Mounting bracket

#### **OMH-ML7-02**

Mounting aid for ML7 and ML8 series, Mounting bracket

### **Description of Sensor Functions**

#### **Adjustment possibilities**

The sensor features an analog output with 2 programmable limits. Programming the limits, the output mode, the output type and the beam width can be done in two different ways:

- Using the sensor's programming button
- Using the IO-link interface of the sensor. This method requires an IO-link master (e.g. IO-link-Master02-USB) and the associated software. The download link is available on the product page for the sensor at www.pepperl-fuchs.de

#### **Synchronization**

The sensor features a synchronization input for suppressing ultrasonic mutual interference ("cross talk").

The following synchronization modes are available:

- 1. Automatic multiplex mode.
- 2. Automatic common mode
- 3. Externally controlled synchronization

#### **Further Documentation**

- For information on programming via programming button and synchronisation you may refer to the commissioning instruction.
- For detailed information on application and programming via IO-Link we provide a manual.