





 ϵ

Model Number

OBT30-R3-E2-0,2M-V31

Triangulation sensor (BGS) with fixed cable and 4-pin, M8 connector


Features

- 45° cable outlet for maximum mounting freedom under extremely tight space constraints
- Improvement in machine availability with abrasion-resistant, antistatic glass front
- Highly visible light spot, even on dark materials
- Precision object detection, almost irrespective of the color

Product information

The nano sensor has been developed for a broad range of applications. It offers excellent durability and is exceptionally easy to install. The housing is compact and, with its 45° cable outlet, can be installed in the smallest spaces. New functional principles and functionality open up a range of new options. The abrasion-resistant lens allows long operating times close to the moving object.

Dimensions



Electrical connection




Pinout

(white) (blue) (black)

Indicators/operating means





1	Operating display	green
2	Signal display	yellow
3	Emitter	
4	Receiver 1	
5	Receiver 2	

FPEPPERL+FUCHS



Technical data General specifications Detection range 1 ... 30 mm standard white, 100 mm x 100 mm Reference target LED Light source Light type modulated visible red light, 630 nm Black/White difference (6 %/90 %) < 7 % at 30 mm Angle deviation approx. 2 Diameter of the light spot approx. 2 mm at a distance of 30 mm Angle of divergence approx. 2 Optical face frontal EN 60947-5-2: 30000 Lux Ambient light limit Functional safety related parameters 800 a $MTTF_d$ Mission Time (T_M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means LED green, statically lit Power on , short-circuit : LED green flas-Operation indicator hing (approx. 4 Hz) Function indicator LED yellow ON: lights when object is detected **Electrical specifications** 10 ... 30 V DC , class 2 Operating voltage U_B No-load supply current < 10 mA I_0 Protection class Ш Output Switching type NO contact Signal output 1 PNP output, short-circuit protected, reverse polarity protected, open collector Switching voltage max. 30 V DC max. 50 mA, resistive load Switching current Voltage drop \leq 1.5 V DC Switching frequency f approx. 800 Hz 600 μs Response time Directive conformity Electromagnetic compatibility Directive 2014/30/EU EN 60947-5-2:2007 EN 60947-5-2/A1:2012 **Ambient conditions** -25 ... 60 °C (-13 ... 140 °F) Ambient temperature -30 ... 70 °C (-22 ... 158 °F) Storage temperature **Mechanical specifications** Housing width 7.5 mm Housing height 24 mm Housing depth 11.2 mm Degree of protection IP67 200 mm fixed cable with 4-pin, M8x1 connector Connection Material PC/ABS and TPU Housing Optical face glass PUR Cable Mass approx. 20 g Cable length 200 mm Approvals and certificates **UL** approval E87056, cULus Recognized, Class 2 Power Source

Accessories

MH-R3-01

Mounting aid for sensors from the R3 series, mounting bracket

MH-R3-02

Mounting aid for sensors from the R3 series, mounting bracket

MH-R3-03

Mounting aid for sensors from the R3 series, mounting bracket

MH-R3-04

Mounting aid for sensors from the R3 series, mounting bracket

V31-GM-2M-PUR

Female cordset, M8, 4-pin, PUR cable

V31-WM-2M-PUR

Female cordset, M8, 4-pin, PUR cable

Other suitable accessories can be found at www.pepperl-fuchs.com

CCC approval

CCC approval / marking not required for products rated ≤36 V

Curves/Diagrams

