





CE

Model Number

OBT15-R2-E2-0,2M-V31


Triangulation sensor (BGS) with fixed cable and 4-pin, M8 connector

Features

- High-performance miniature photoe-٠ lectric sensors
- 45° cable outlet for maximum moun-٠ ting freedom under extremely tight space constraints
- Improvement in machine availability ٠ with abrasion-resistant, antistatic glass front
- Extremely small light spot for very high switching point accuracy
- Highly visible light spot, even on dark materials
- Precision object detection, almost ir-• respective of the color

Product information

The nano sensor has been developed for a broad range of applications. It offers excellent durability and is exceptionally easy to install. The housing is compact and, with its 45° cable outlet, can be installed in the smallest spaces. New functional principles and functionality open up a range of new options. The abrasion-resistant lens allows long operating times close to the moving object.




Electrical connection



Pinout



Indicators/operating means



1	Operating display	green
2	Signal display	yellow
3	Emitter	
4	Receiver	

Germany: +49 621 776 4411

Singapore: +65 6779 9091



www.pepperl-fuchs.com

fa-info@us.pepperl-fuchs.com

fa-info@de.pepperl-fuchs.com

fa-info@sg.pepperl-fuchs.com

Mounting aid for R2 series, Mounting bra-

Female cordset, M8, 4-pin, PUR cable

Female cordset, M8, 4-pin, PUR cable Other suitable accessories can be found at

Accessories MH-R2-01

cket

cket

cket

cket

MH-R2-02

MH-R2-03

MH-R2-04

V31-GM-2M-PUR

V31-WM-2M-PUR

www.pepperl-fuchs.com

Technical data

Technical data				
General specifications				
Detection range		2 15 mm		
Reference target		standard white, 100 mm x 100 mm		
Light source		LED		
Light type		modulated visible red light , 630 nm		
Black/White difference (6 %/90 %)		< 5 % at 15 mm		
Angle deviation		approx. 2 °		
Diameter of the light spot		approx. 2 mm at a distance of 15 mm		
Angle of divergence		approx. 2 °		
Optical face		frontal		
Ambient light limit		EN 60947-5-2 : 30000 Lux		
Functional safety related parameters				
MTTF _d		800 a		
Mission Time (T _M)		20 a		
Diagnostic Coverage (DC)		0 %		
Indicators/operating means				
Operation indicator		LED green, statically lit Power on , short-circuit : LED green flashing (approx. 4 Hz)		
Function indicator		LED yellow ON: lights when object is detected		
Electrical specifications				
Operating voltage	UB	10 30 V DC , class 2		
No-load supply current	I ₀	< 10 mA		
Output				
Switching type		NO contact		
Signal output		1 PNP output, short-circuit protected, reverse polarity protected, open collector		
Switching voltage		max. 30 V DC		
Switching current		max. 50 mA , resistive load		
Voltage drop	U _d	≤ 1.5 V DC		
Switching frequency	f	approx. 800 Hz		
Response time		600 µs		
Ambient conditions				
Ambient temperature		-25 60 °C (-13 140 °F)		
Storage temperature		-30 70 °C (-22 158 °F)		
Mechanical specifications				
Housing width		7.5 mm		
Housing height		24 mm		
Housing depth		11.2 mm		
Degree of protection		IP67		
Connection		200 mm fixed cable with 4-pin, M8x1 connector		
Material				
Housing		PC/ABS and TPU		
Optical face		glass		
Cable		PUR		
Installation		Fixing screws , 2 x M2 allen head screws included with delivery		
Mass Cable length		approx. 20 g		
Cable length 200 mm				
Compliance with standards and directi- ves				
Directive conformity				
EMC Directive 2004/108/EC		EN 60947-5-2:2007		
Approvals and certificates				
UL approval		cULus Recognized, Class 2 Power Source		
CCC approval		CCC approval / marking not required for products rated ${\leq}36~V$		


2


486 0001 Germany: +49

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Curves/Diagrams





Release date: 2017-07-17 13:38 Date of issue: 2017-07-17 262344_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

