





 ϵ

Model Number

OBT50-R3-E2-0,2M-V31

Triangulation sensor (BGS) with fixed cable and 4-pin, M8 connector


Features

- 45° cable outlet for maximum mounting freedom under extremely tight space constraints
- Improvement in machine availability with abrasion-resistant, antistatic glass front
- Highly visible light spot, even on dark materials
- Precision object detection, almost irrespective of the color
- Extremely long detection range paves the way for new applications

Product information

The nano sensor has been developed for a broad range of applications. It offers excellent durability and is exceptionally easy to install. The housing is compact and, with its 45° cable outlet, can be installed in the smallest spaces. New functional principles and functionality open up a range of new options. The abrasion-resistant lens allows long operating times close to the moving object.

Dimensions



Electrical connection




Pinout



(white) (blue) (black)

Indicators/operating means





1	Operating display	green
2	Signal display	yellow
3	Emitter	
4	Receiver 1	
5	Receiver 2	

Technical data				
General specifications				
Detection range		3 50 mm		
Reference target		standard white, 100 mm x 100 mm		
Light source		LED		
Light type		modulated visible red light, 630 nm		
Black/White difference (6 %/90 %	6)	< 15 % at 50 mm		
Angle deviation		approx. 2 °		
Diameter of the light spot		approx. 3.5 mm at a distance of 50 mm		
Angle of divergence		approx. 2 °		
Optical face		frontal		
Ambient light limit		EN 60947-5-2 : 30000 Lux		
Functional safety related parameters				
MTTF _d		800 a		
Mission Time (T _M)		20 a		
Diagnostic Coverage (DC)		0 %		
Indicators/operating means				
Operation indicator		LED green, statically lit Power on , short-circuit : LED green flas hing (approx. 4 Hz)		
Function indicator		LED yellow ON: lights when object is detected		
Electrical specifications				
Operating voltage	U_{B}	10 30 V DC , class 2		
No-load supply current	I _O	< 10 mA		
Protection class	U	·		
Output				
Switching type		NO contact		
Signal output		1 PNP output, short-circuit protected, reverse polarity protected open collector		
Switching voltage		max. 30 V DC		
Switching current		max. 50 mA , resistive load		
Voltage drop	Ud	≤ 1.5 V DC		
Switching frequency	f	approx. 800 Hz		
Response time	•	600 µs		
Directive conformity				
Electromagnetic compatibility				
Directive 2014/30/EU		EN 60947-5-2:2007 EN 60947-5-2/A1:2012		
Ambient conditions		EN 00047 3 2.2007 EN 00047 3 2/A1.2012		
		05 00 00 / 10 140 05\		
Ambient temperature		-25 60 °C (-13 140 °F) -30 70 °C (-22 158 °F)		
Storage temperature		-30 70 C (-22 136 F)		
Mechanical specifications				
Housing width		7.5 mm		
Housing height		24 mm		
Housing depth		11.2 mm		
Degree of protection		IP67		
Connection		200 mm fixed cable with 4-pin, M8x1 connector		
Material		DO(ADO ATRIA		
Housing		PC/ABS and TPU		
Optical face		glass		
Cable		PUR		
Mass		approx. 20 g		
Cable length		200 mm		
Approvals and certificates				
• •		E97056 al II up Boognized Class & Bourse Course		
UL approval		E87056, cULus Recognized, Class 2 Power Source		

Accessories

MH-R3-01

Mounting aid for sensors from the R3 series, mounting bracket

MH-R3-02

Mounting aid for sensors from the R3 series, mounting bracket

MH-R3-03

Mounting aid for sensors from the R3 series, mounting bracket

MH-R3-04

Mounting aid for sensors from the R3 series, mounting bracket

V31-WM-2M-PUR

Female cordset, M8, 4-pin, PUR cable

V31-GM-2M-PUR

Female cordset, M8, 4-pin, PUR cable

Other suitable accessories can be found at www.pepperl-fuchs.com

EPPERL+FUCHS

CCC approval

CCC approval / marking not required for products rated \leq 36 V

Curves/Diagrams

