

CH-W-H-A11-PPZZR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Charging solutions for the home
Just charge. Done. Off you go!

General ordering data

Version	Wallbox, max. charging capacity of 11 kW @ 3-phase (400 V) grid connection, max. current 16 A, Attached 5m charging cable type 2, Modbus RTU
Order No.	2781350000
Type	CH-W-H-A11-PPZZR
GTIN (EAN)	4064675055747
Qty.	1 pc(s).

Creation date April 21, 2021 3:31:18 PM CEST

Catalogue status 09.04.2021 / We reserve the right to make technical changes.

CH-W-H-A11-PPZZZR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	109 mm	Depth (inches)	4.291 inch
Height	486 mm	Height (inches)	19.134 inch
Net weight	6,060 g	Weight	9,500 g
Width	351 mm	Width (inches)	13.819 inch

Temperatures

Storage temperature	-40 °C...70 °C	Humidity at storage temperature	5 - 95% rel. humidity
Operating temperature	-25 °C...50 °C		

Assembly

Installation	Mounting plate
--------------	----------------

Features

On- / Off-Switch integrated	Yes	Automatic plug unlocking in case of power loss available	Yes
Plug lock available	Yes	Status display available	Yes
Welding detection	Yes	Failure shutdown	Yes
Failure shutdown method	All-pole	DC - residual current detection integrated	Yes
Type of integrated residual current detection	DC residual current sensor	DC - residual current	6 mA
AC - residual current detection integrated	No	AC - residual current	30 mA
Type of residual current detection to be provided by the installation	RCD Type A	User authentication	No
With energy meter	No	Billing options in compliance with German calibration law	No
Load management available	Yes	Load management type	DI, Modbus RTU
Communication integrated	Yes	Type of communication	Modbus RTU

Housing

Operating altitude	≤ 2000 m	Design Cover exchangeable	Yes
Housing main material	Polycarbonate glass fiber reinforced	Colour	black

System requirements

Connection system	Attached 5m charging cable type 2	Type of communication to vehicle	Control Pilot (CP), Proximity Pilot / Plug Present (PP)
Charge mode	Mode 3	Protection class	I
Surge voltage category	III	Pollution severity	3

Approvals and norms

Approvals	IEC 61851-1, IEC 61851-21-1, IEC 61851-21-2, IEC 62196-1, IEC 62196-2, EN 50620
-----------	---

CH-W-H-A11-PPZZZR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Connection data (input)**

Mains frequency	50 Hz	Type of connection	Screw terminal connectors
Wire size ,max.	6 mm ²	With circuit breaker	No

Performance specification

Performance specification	Number of phases input	3
	Input voltage type	AC
	Input voltage	400 V
	Input current, max.	16 A
	Charging power, max	11 kW

Classifications

ETIM 6.0	EC002883	ETIM 7.0	EC002883
ECLASS 9.0	27-14-47-01	ECLASS 9.1	27-14-47-01
ECLASS 10.0	27-14-47-01	ECLASS 11.0	27-14-47-01

Downloads

User Documentation	Sicherheitshinweise Montageanleitung Bedienungsanleitung Bedienungsanleitung Vernetzung
Brochure/Catalogue	Catalogues in PDF-format

CH-W-H-A11-PPZZZR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensional drawing

