

Router - FL MGuard GT/GT

2700197

<https://www.phoenixcontact.com/pc/products/2700197>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Security appliance, 10/100/1000 Mbps, NAT, advanced firewall, SFP combo ports, functionally extendable with licenses

Your advantages

- Intelligent stateful inspection firewall
- Central management tool
- Secure remote services (VPN) according to IPsec standard
- Replaceable configuration memory
- Fast operation by means of configuration and remote maintenance portal
- Comprehensive connection options
- Flexible routing

Commercial Data

Item number	2700197
Packing unit	1 pc
Minimum order quantity	1 pc
Product Key	DNN311
Catalog Page	Page 335 (C-6-2019)
GTIN	4046356499651
Weight per Piece (including packing)	828 g
Weight per Piece (excluding packing)	660 g
Customs tariff number	85176200
Country of origin	DE

Technical Data

Dimensions

Width	128 mm
Height	110 mm
Depth	69 mm

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Material specifications

Color	gray aluminum
Housing material	Metal

Interfaces

Ethernet (combo)

Connection method	Combo
Note on the connection method	Either SFP port or RJ45 port active
Transmission speed	10/100/1000 Mbps (SFP module: 100/1000 Mbps)
Transmission physics	Copper or SFP module
Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity
No. of channels	2 (Combo ports)

Serial (RS-232)

Connection method	RS-232-C, 6-pos. MINI-DIN socket (PS/2)
-------------------	---

Fiber optic interface

Connection method	SFP ports
Transmission speed	1000 Mbps (full duplex)
Transmission physics	Depending on the SFP module
Transmission length	up to 80 km (Depending on the fiber/SFP module used)

Product properties

Type	Stand-alone
Product type	Security router for the DIN rail

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Security functions

Number of VPN tunnels	0 (up to 250 tunnels with additional license as an option)
Data integrity	MD5, SHA-1, SHA 256, SHA-512

Dynamic Host Configuration Protocol (DHCP) support	Server or Relay Agent
Filtering	MAC and IP addresses, ports, protocols
Firewall data throughput	max. 417 Mbps (Router mode, default firewall rules, bidirectional throughput)
	max. 174 Mbps (Stealth mode, default firewall rules, bidirectional throughput)
Firewall rules	Configurable stateful inspection firewall
Basic functions	Router with intelligent firewall and Gigabit connectivity
Link Layer Discovery Protocol (LLDP)	As per protocol 802.2
Network Time Protocol (NTP) client	Client
Remote Syslog Logging	On external server
Routing	Standard routing, NAT, 1:1-NAT, port forwarding
Protection against	IP spoofing, DoS and Syn Flood Protection
Encryption methods	DES, 3DES, AES-128, -192, -256
Virtual private network (VPN) throughput	max. 106 Mbps (Router mode, VPN bidirectional throughput)

Electrical properties

Power consumption	6.5 W
Maximum power dissipation for nominal condition	6.48 W
Test voltage	500 V DC
Test section	for one minute 500 V DC

Supply

Supply voltage	24 V DC (redundant)
Supply voltage range	18 V DC ... 32 V DC
Power supply connection	Via COMBICON, max. conductor cross section 2.5 mm ²
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Max. current consumption	270 mA
Typical current consumption	270 mA (at U _S = 24 V DC)

Function

Signal contact control voltage	24 V DC (typical)
Signal contact control current	270 mA (typical)

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Shock	DIN EN 60068-2-27
Vibration (operation)	in accordance with IEC 60068-2-6: 5g, 10 Hz ... 150 Hz
Air pressure (operation)	86 hPa ... 108 kPa (1500 m above sea level)
Air pressure (storage/transport)	66 hPa ... 108 kPa (3500 m above sea level)

Standards and regulations

Router - FL MGUARD GT/GT



2700197

<https://www.phoenixcontact.com/pc/products/2700197>

Free from substances that could impair the application of coating	In acc. with VW specification
---	-------------------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

EMC data

Conformance with EMC directives	IEC 61000-6-2 IEC 61000-4-2 (ESD) 6 kV contact discharge, 8 kV air discharge
	IEC 61000-6-2 IEC 61000-4-3 (immunity to radiated interference) 10 V/m (80 MHz ... 2000 MHz)
	IEC 61000-6-2 IEC 61000-4-4 (burst) 2 kV power line, 1kV data line
	IEC 61000-6-2 IEC 61000-4-5 (surge) power line: 2 kV (line/earth), 1 kV (line/line), 1 kV data line
	IEC 61000-6-2 IEC 61000-4-6 (immunity to conducted interference) 3 V (10 kHz ... 150 kHz), 10 V (150 kHz ... 80 MHz)
Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise emission	EN 61000-6-4
Noise immunity	EN 61000-6-2:2005

LED signaling

Status display	LEDs: LNK, Mode, Inf, ACT, SPD, FD, US1, US2, Fail, and 7-segment display
----------------	---

Router - FL MGuard GT/GT



2700197

<https://www.phoenixcontact.com/pc/products/2700197>

Approvals



EAC

Approval ID: RU*DE*08.B.00731/19



DNV GL

Approval ID: TAA00002CU



LR

Approval ID: LR22191720TA



BV

Approval ID: 42674/B0 BV



UL Listed

Approval ID: FILE E 238705



cUL Listed

Approval ID: FILE E 238705



RINA

Approval ID: ELE121121XG

cULus Listed

Router - FL MGuard GT/GT



2700197

<https://www.phoenixcontact.com/pc/products/2700197>

Classifications

ECLASS

ECLASS-9.0	19170103
ECLASS-10.0.1	19170406
ECLASS-11.0	19170406

ETIM

ETIM 8.0	EC001478
----------	----------

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

Router - FL MGUARD GT/GT



2700197

<https://www.phoenixcontact.com/pc/products/2700197>

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Router - FL MGUARD GT/GT

2700197

<https://www.phoenixcontact.com/pc/products/2700197>



Accessories

Patch cable

Patch cable - FL CAT5 PATCH 0,3 - 2832250

<https://www.phoenixcontact.com/pc/products/2832250>

Patch cable, CAT5, assembled, 0.3 m



Patch cable

Patch cable - FL CAT5 PATCH 0,5 - 2832263

<https://www.phoenixcontact.com/pc/products/2832263>

Patch cable, CAT5, assembled, 0.5 m



Router - FL MGuard GT/GT

2700197

<https://www.phoenixcontact.com/pc/products/2700197>



Patch cable

Patch cable - FL CAT5 PATCH 1,0 - 2832276

<https://www.phoenixcontact.com/pc/products/2832276>

Patch cable, CAT5, assembled, 1 m



Patch cable

Patch cable - FL CAT5 PATCH 1,5 - 2832221

<https://www.phoenixcontact.com/pc/products/2832221>

Patch cable, CAT5, assembled, 1.5 m



Router - FL MGuard GT/GT

2700197

<https://www.phoenixcontact.com/pc/products/2700197>



Patch cable

Patch cable - FL CAT5 PATCH 2,0 - 2832289

<https://www.phoenixcontact.com/pc/products/2832289>



Patch cable, CAT5, assembled, 2 m

Patch cable

Patch cable - FL CAT5 PATCH 3,0 - 2832292

<https://www.phoenixcontact.com/pc/products/2832292>



Patch cable, CAT5, assembled, 3 m

Router - FL MGuard GT/GT

2700197

<https://www.phoenixcontact.com/pc/products/2700197>



Patch cable

Patch cable - FL CAT5 PATCH 5,0 - 2832580

<https://www.phoenixcontact.com/pc/products/2832580>



Patch cable, CAT5, assembled, 5 m

Patch cable

Patch cable - FL CAT5 PATCH 7,5 - 2832616

<https://www.phoenixcontact.com/pc/products/2832616>



Patch cable, CAT5, assembled, 7.5 m

Router - FL MGuard GT/GT

2700197

<https://www.phoenixcontact.com/pc/products/2700197>



Patch cable

Patch cable - FL CAT5 PATCH 10,0 - 2832629

<https://www.phoenixcontact.com/pc/products/2832629>

Patch cable, CAT5, assembled, 10 m




Patch cable

Patch cable - FL CAT6 PATCH 12,5 - 2891369

<https://www.phoenixcontact.com/pc/products/2891369>

Patch cable, CAT6, pre-assembled, 12.5 m



Router - FL MGuard GT/GT

2700197


<https://www.phoenixcontact.com/pc/products/2700197>



Patch cable

Patch cable - FL CAT6 PATCH 15,0 - 2891372

<https://www.phoenixcontact.com/pc/products/2891372>




Patch cable, CAT6, pre-assembled, 15.0 m

Patch cable

Patch cable - FL CAT6 PATCH 20,0 - 2891576

<https://www.phoenixcontact.com/pc/products/2891576>



Patch cable, CAT6, pre-assembled, 20.0 m

Router - FL MGUARD GT/GT

2700197


<https://www.phoenixcontact.com/pc/products/2700197>



Dust protection

Dust protection - FL RJ45 PROTECT CAP - 2832991

<https://www.phoenixcontact.com/pc/products/2832991>



Dust protection caps for RJ45 socket

RJ45 connector

RJ45 connector - FL PLUG RJ45 GR/2 - 2744856

<https://www.phoenixcontact.com/pc/products/2744856>



RJ45 connector, shielded, with bend protection sleeve, 2 pieces, gray for straight cables, for assembly on site. For connections that are not crossed, it is recommended that you use the connector set with gray bend protection sleeve.

Router - FL MGuard GT/GT

2700197


<https://www.phoenixcontact.com/pc/products/2700197>



RJ45 connector

RJ45 connector - FL PLUG RJ45 GN/2 - 2744571

<https://www.phoenixcontact.com/pc/products/2744571>



RJ45 connector, shielded, with bend protection sleeve, 2 pieces, green for crossed cables, for assembly on site. For connections that are crossed, it is recommended that the connector set with green bend protection sleeves is used.

Assembly tool

Assembly tool - FL CRIMPTOOL - 2744869

<https://www.phoenixcontact.com/pc/products/2744869>



Crimping pliers, for assembling the RJ45 plugs FL PLUG RJ45..., for assembly on site

Router - FL MGuard GT/GT

2700197

<https://www.phoenixcontact.com/pc/products/2700197>

Configuration memory

Configuration memory - FL MEM PLUG - 2891259

<https://www.phoenixcontact.com/pc/products/2891259>



Exchangeable configuration memory of the device settings for simple device exchange and set-up

License

License - FL MGuard LIC LIFETIME FW - 2700184

<https://www.phoenixcontact.com/pc/products/2700184>



License for lifetime software update of FL MGuard field devices.

Router - FL MGUARD GT/GT

2700197

<https://www.phoenixcontact.com/pc/products/2700197>

License

License - FL MGUARD LIC CIM - 2701083

<https://www.phoenixcontact.com/pc/products/2701083>



License for activating CIFS Integrity Monitoring (CIM) on an FL MGUARD

License

License - FL MGUARD LIC VPN-250 GROUP - 2700192

<https://www.phoenixcontact.com/pc/products/2700192>



License for up to 250 additional VPN online connections

Router - FL MGUARD GT/GT

2700197

<https://www.phoenixcontact.com/pc/products/2700197>



License

License - FL MGUARD LIC VPN-250 - 2700193

<https://www.phoenixcontact.com/pc/products/2700193>



License for up to 250 additional VPN online connections

License

License - FL MGUARD LIC VPN-10 - 2700194

<https://www.phoenixcontact.com/pc/products/2700194>



License for up to 10 additional VPN online connections

Router - FL MGUARD GT/GT

2700197

<https://www.phoenixcontact.com/pc/products/2700197>

License

License - MGUARD SECURE VPN CLIENT LIC - 2702579

<https://www.phoenixcontact.com/pc/products/2702579>



License for mGuard Secure VPN Client v11.x

Software

Software - FL MGUARD DM UNLIMITED - 2981974

<https://www.phoenixcontact.com/pc/products/2981974>



Central device management software for MGUARD devices for any number of devices in the field. For installation on a PC. No additional licenses required. Download trial version for up to 10 devices.

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG

Flachsmarktstraße 8

D-32825 Blomberg

+49 (0) 5235-3 00

info@phoenixcontact.com