

## IE-ANT-CELL/WL-MB-MIMO-DO

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### Antennas and antenna accessories (coax cables and mounts)

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

### General ordering data

Version	Omni-directional antenna, Cellular antenna, Wi-Fi antenna, Up to 5G (NR), Up to Wi-Fi 6 & 6E (IEEE802.11ax), Linear, Vertical, 2x SMA male, 2x RP-SMA male, IP67, Impedance: 50 Ω
Order No.	<a href="#">2788090000</a>
Type	IE-ANT-CELL/WL-MB-MIMO-DO
GTIN (EAN)	4064675066354
Qty.	1 pc(s).

Creation date March 10, 2023 8:36:05 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## IE-ANT-CELL/WL-MB-MIMO-DO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	90 mm	Height (inches)	3.543 inch
Diameter	132 mm	Net weight	627 g

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	85 °C

## Enclosure material

Colour	white
--------	-------

## Included in delivery

Included in delivery	1 x antenna
----------------------	-------------

## Mechanical and material properties of cable

Cable length	1 m	Min. bending radius, repetitive	25 mm
--------------	-----	---------------------------------	-------

## Technical data

Amount of antenna elements (MIMO)	2	Antenna gain	2.5 dBi, 3-4 dBi
Composite power max.	50 W	Frequency range	690-950 MHz, 1.7-3.8 GHz, 2.4-2.5 GHz, 4.9-7.125 GHz
Impedance	50 Ω	Polarisation	Linear, Vertical
Standing wave ratio	< 2.0 typical, 3.5 max.	Type of connection	2x SMA male, 2x RP-SMA male

## Environmental conditions

Operating temperature, max.	85 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	85 °C	Storage temperature, min.	-40 °C

## Classifications

ETIM 6.0	EC001698	ETIM 7.0	EC001698
ETIM 8.0	EC001698	ECLASS 9.0	19-07-01-05
ECLASS 9.1	19-07-01-05	ECLASS 10.0	19-07-01-05
ECLASS 11.0	19-07-01-05	ECLASS 12.0	19-07-01-05

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	e4cad7fc-a55e-4d5c-8f05-417a6385e9b6

## Approvals

ROHS	Conform
------	---------

**IE-ANT-CELL/WL-MB-MIMO-DO**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

---

Engineering Data	<a href="#">CAD data – STEP</a>
Technical Documentation	<a href="#">Radiation Pattern</a>
User Documentation	<a href="#">Hardware Installation Guide</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

---