

## Mod. 2712HL.B


2712HL – EXPLORER CASES, ULTRALIGHT WATERPROOF CASE

Small size watertight case injected with proprietary copolymer PP that makes it more resistant and lightweight than other similar products. IP67 and MIL Stan certified to be resistant to impact, liquids, shocks. Ideal storage for documents, tablets, small mobile devices, tools and more.

- Metal reinforced padlock holes
- Single block high performance injected O-ring
- Automatic pressure valve
- Soft rubber handle grip
- Removable lid
- Anti-tilt support
- Certified to grant constant performances between -33°C and +90 °C.
- Six standard colors available



METRIC MM-KG-C°



### INTERNAL DIMENSIONS

<b>L LENGTH</b>	276 mm
<b>W WIDTH</b>	200 mm
<b>D DEPTH</b>	120 mm
<b>LID</b>	35 mm
<b>BASE</b>	85 mm


### EXTERNAL DIMENSIONS

<b>L LENGTH</b>	316 mm
<b>W WIDTH</b>	270 mm
<b>D DEPTH</b>	143 mm

### OTHER DATA

<b>WEIGHT EMPTY</b>	1.29 Kg
<b>WEIGHT WITH FOAM</b>	1.5 Kg
<b>WEIGHT WITH CUSTOM FOAM</b>	Kg
<b>VOLUME</b>	6.60 lt
<b>BUOYANCY</b>	4.20 Kg/max
<b>OPERATING TEMPERATURE</b>	°C min -33 / max +90

IMPERIAL IN-LBS-F°



**INTERNAL DIMENSIONS**

<b>L LENGTH</b>	10 7/8 in
<b>W WIDTH</b>	7 7/8 in
<b>D DEPTH</b>	4 3/4 in
<b>LID</b>	1 3/8 in
<b>BASE</b>	3 3/8 in

**EXTERNAL DIMENSIONS**

<b>L LENGTH</b>	12 7/16 in
<b>W WIDTH</b>	10 5/8 in
<b>D DEPTH</b>	5 5/8 in

**OTHER DATA**

<b>WEIGHT EMPTY</b>	2.84 lbs
<b>WEIGHT WITH FOAM</b>	3.30 lbs
<b>WEIGHT WITH CUSTOM FOAM</b>	lbs
<b>VOLUME</b>	1.74 gal
<b>BUOYANCY</b>	9.25 lbs/max
<b>OPERATING TEMPERATURE</b>	°F min -27.4 / max +194