

**IE-ANT-WL-DB-MIMO-PD-RPSMAM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Antennas and antenna accessories (coax cables and mounts)**

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

**General ordering data**

Version	Semi-directional antenna, Wi-Fi antenna, Up to Wi-Fi 6 & 6E (IEEE802.11ax), +/- 45° linear, 2x RP-SMA male, IP67, Impedance: 50 Ω
Order No.	<a href="#">2788080000</a>
Type	IE-ANT-WL-DB-MIMO-PD-RPSMAM
GTIN (EAN)	4064675066347
Qty.	1 pc(s).

Creation date March 10, 2023 8:36:58 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

**IE-ANT-WL-DB-MIMO-PD-RPSMAM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Height	34 mm	Height (inches)	1.339 inch
Width	198 mm	Width (inches)	7.795 inch
Diameter	137 mm	Net weight	450 g

**Temperatures**

Storage temperature	-40 °C...70 °C	Operating temperature	-40 °C...70 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	70 °C

**Enclosure material**

Colour	white
--------	-------

**Included in delivery**

Included in delivery	1 x antenna
----------------------	-------------

**Mechanical and material properties of cable**

Cable length	0.78 m
--------------	--------

**Technical data**

Amount of antenna elements (MIMO)	2	Antenna gain	6 dBi, 5 dBi
Composite power max.	20 W	Frequency range	2.3-2.8 GHz, 4.9-7.125 GHz
Impedance	50 Ω	Polarisation	+/- 45° linear
Standing wave ratio	< 2.0 typical, 2.5 max.	Type of connection	2x RP-SMA male

**Environmental conditions**

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	70 °C	Storage temperature, min.	-40 °C
Wind load	200 km/h		

**Classifications**

ETIM 6.0	EC001698	ETIM 7.0	EC001698
ETIM 8.0	EC001698	ECLASS 9.0	19-07-01-05
ECLASS 9.1	19-07-01-05	ECLASS 10.0	19-07-01-05
ECLASS 11.0	19-07-01-05	ECLASS 12.0	19-07-01-05

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	e4cad7fc-a55e-4d5c-8f05-417a6385e9b6

**Approvals**

ROHS	Conform
------	---------

**IE-ANT-WL-DB-MIMO-PD-RPSMAM**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Technical Documentation	<a href="#">Radiation Pattern</a>
User Documentation	<a href="#">Hardware Installation Guide</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>