

# Measuring instrument - EEM-MB370 - 2907954

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Multi-functional energy measuring device without display with integrated Modbus/TCP interface for measuring electrical parameters in low-voltage installations up to 690 V.



## Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4055626498331
Weight per Piece (excluding packing)	260.000 g
Custom tariff number	90303100
Country of origin	Germany
Note	Made to Order (non-returnable)

## Technical data

### Dimensions

Width	90 mm
Height	90 mm
Depth	71.7 mm

### Ambient conditions

Ambient temperature (operation)	-10 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Maximum altitude	≤ 2000 m
Max. permissible relative humidity (operation)	≤ 95 % (non-condensing)
Degree of protection	IP20 (Housing)

### Input data

Measuring principle	True r.m.s. value measurement
Acquisition of harmonics	up to 63rd harmonic
Measured value	AC sine (50/60 Hz)

# Measuring instrument - EEM-MB370 - 2907954

## Technical data

### Input data

Input name	Voltage measuring input V1, V2, V3
Input voltage range	35 V AC ... 690 V AC (Phase/Phase)
	20 V AC ... 400 V AC (Phase/neutral conductor)
	60 V AC ... 2000000 V AC (primary)
	60 V AC ... 400 V AC (secondary)
Surge voltage capacity	760 V AC (Phase/Phase)
Precision	0.2 %
Input name	Current measurement I1, I2, I3
Input current	1 A (secondary)
	5 A (secondary)
Current measuring range	1 A ... 20000 A (primary)
Overload capacity	6 A ( $I_{max}$ )
Response threshold from measuring range nominal value	10 mA (1 A)
Precision	0.2 %
Current overload	50 A for 1 s
Precision	0.5 %
Active energy (IEC 62053-22)	Class 0.5 S
Reactive power (IEC 62053-23)	Class 2
Description of the input	Digital input in accordance with IEC/EN 61131-2 (type 3)
Number	1
Voltage input signal	0 V DC ... 30 V DC
Current input signal	2 mA ... 15 mA

### Output data

Output description	Digital output in accordance with IEC/EN 61131-2 (type 3)
Number	1
Current output signal	$\leq 100$ mA

### Device interface

Designation	Network interface
Communication protocol	Modbus/TCP
	REST
Connection method	RJ45

### General

Supply voltage range	100 V AC ... 230 V AC ( $\pm 20$ %)
	150 V DC ... 250 V DC ( $\pm 20$ %)
Power consumption	$\leq 4$ W
Mains type	3-phase (3 or 4-wire), 2-phase (2-wire), and single-phase (1-wire)
Color	gray
Conformance	CE-compliant
Test voltage	4 kV AC (50 Hz, 1 min.)

# Measuring instrument - EEM-MB370 - 2907954

## Technical data

### General

Product family	EMpro
----------------	-------

### Connection data

Connection name	Current / voltage / supply
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section solid	0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Conductor cross section flexible	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross section AWG	24 ... 10
Torque	0.5 Nm ... 0.6 Nm

### Connection data 2

Connection name	Digital I/O / communication
Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross section solid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross section AWG	26 ... 14
Torque	0.5 Nm ... 0.6 Nm

### UL data

Operating mode	Indoor use
----------------	------------

### Standards and Regulations

Conformance	CE-compliant
-------------	--------------

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 10.0.1	27142330
eCl@ss 8.0	27142330
eCl@ss 9.0	27142330

### ETIM

ETIM 5.0	EC002301
ETIM 6.0	EC002301

# Measuring instrument - EEM-MB370 - 2907954

## Classifications

ETIM

ETIM 7.0	EC002301
----------	----------

## Approvals

Approvals

Approvals

EAC / UL Listed / cUL Listed / cULus Listed

Ex Approvals

## Approval details

EAC		RU*DE*08.B.00734/19
-----	--	---------------------

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 357804
-----------	--	---	---------------

cUL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 357804
------------	--	---	---------------

cULus Listed			
--------------	--	--	--

## Accessories

Accessories

Current transformer

Current transformer - PACT MCR-V2-3015-60-PT - 2907413



Window-type current transformer with screw and Push-in connection technology, conductor connection for Push-in: from directly above, no tools required. The following can be selected: primary current (50 ... 750) A AC, secondary current (1 or 5) A AC, accuracy class 0.5 or 1, VA power

## Measuring instrument - EEM-MB370 - 2907954

### Accessories

#### Current transformer - PACT MCR-V2-4012-70-PT - 2907414



Window-type current transformer with screw and Push-in connection technology, conductor connection for Push-in: from directly above, no tools required. The following can be selected: primary current (100 ... 1000) A AC, secondary current (1 or 5) A AC, accuracy class 0.5 or 1, VA power

---

#### Current transformer - PACT MCR-V2-5012-85-PT - 2907416



Window-type current transformer with screw and Push-in connection technology, conductor connection for Push-in: from directly above, no tools required. The following can be selected: primary current (100 ... 1500) A AC, secondary current (1 or 5) A AC, accuracy class 0.5 or 1, VA power

---

#### Current transformer - PACT MCR-V2-6015-85-PT - 2907417



Window-type current transformer with screw and Push-in connection technology, conductor connection for Push-in: from directly above, no tools required. The following can be selected: primary current (200 ... 1600) A AC, secondary current (1 or 5) A AC, accuracy class 0.5 or 1, VA power

---

#### Current transformer - PACT MCR-V1-21-44 - 2277268



Bus-bar current transformer, primary current can be selected between 50...500 A AC; secondary current can be selected as 1 A AC or 5 A AC; accuracy class can be selected as 0.5 or 1; rated power can be selected

---

#### Current transformer - PACT MCR-V2- 3015- 60 - 2277271



Window-type current transformer, primary current can be selected between 50...750 A AC; secondary current can be selected as 1 A AC or 5 A AC; accuracy class can be selected as 0.5 or 1; rated power can be selected

---

## Measuring instrument - EEM-MB370 - 2907954

### Accessories

Current transformer - PACT MCR-V2- 4012- 70 - 2277284



Window-type current transformer, primary current can be selected between 75...1000 A AC; secondary current can be selected as 1 A AC or 5 A AC; accuracy class can be selected as 0.5 or 1; rated power can be selected

Current transformer - PACT MCR-V2- 5012- 85 - 2277297



Window-type current transformer, primary current can be selected between 100...1500 A AC; secondary current can be selected as 1 A AC or 5 A AC; accuracy class can be selected as 0.5 or 1; rated power can be selected

Current transformer - PACT MCR-V2- 6015- 85 - 2277336



Window-type current transformer, primary current can be selected between 200 ... 1,250 A AC; secondary current can be selected as 1 A AC or 5 A AC; accuracy class can be selected as 0.5 or 1; rated power can be selected

Current transformer - PACT MCR-V2-10020-129 - 2277378



Window-type current transformer, primary current can be selected between 800 and 4,000 A AC, secondary current can be selected 1 A AC or 5 A AC, accuracy class can be selected 0.5 or 1, rated power can be selected

Current transformer - PACT MCR-V3-60 - 2277417



Winding current transformer, primary current can be selected between 1...40 A AC; secondary current can be selected as 1 A AC or 5 A AC; accuracy class can be selected as 0.5 or 1; rated power can be selected