

Measuring instrument - EEM-EM377



2908590

<https://www.phoenixcontact.com/pc/products/2908590>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Three-phase power meter for active power measurement with direct measurement in networks of up to 500 V / 80 A, with S0 output, Ethernet interface, certified in accordance with the MID directive



Commercial Data

Item number	2908590
Packing unit	1 pc
Minimum order quantity	1 pc
Product Key	CK4C11
Catalog Page	Page 205 (C-5-2019)
GTIN	4055626338279
Weight per Piece (including packing)	583.2 g
Weight per Piece (excluding packing)	583.2 g
Customs tariff number	90283019
Country of origin	IT

Technical Data

Product properties

Product type	Energy meter
--------------	--------------

Insulation characteristics

Protection class	II (EN 50470-1)
Pollution degree	2

Electrical properties

Electric strength	6 kV
	4 kV (EN 50470-3, 7.2)

Supply

Supply voltage range	Supply from the measuring circuit
----------------------	-----------------------------------

Input data

Measurement

Input voltage range	3x 184 V ... 288 V (320 V ... 500 V)
Input current range	0.02 A ... 80 A
Power consumption	3.5 VA (1 W)
Frequency range	45 Hz ... 65 Hz
Start current I_{st}	0.02 A
Minimal current I_{min}	0.25 A
Maximum current I_{max}	80 A
Transient current I_{tr}	0.5 A
Nominal current I_{ref}	5 A
Current transformer load	1.5 mΩ
Energy (EN 50470-3)	Class B
Real energy (IEC 62053-21)	Class 1
Reactive power (IEC 62053-23)	Class 2

Output data

S0 output

Output description	Passive opto-isolated
Maximum switching voltage	27 V DC
Max. switching current	27 mA
Pulse time	50 ms ±2 ms
Pause time	30 ms ±2 ms
Pulse LED	1000 imp/kWh
Meter constant	100 imp/kWh, kVAh, kvarh

Connection data

Measuring instrument - EEM-EM377



2908590

<https://www.phoenixcontact.com/pc/products/2908590>

Measurement connection

Connection method	Screw connection
Conductor cross section solid	1.5 mm ² ... 35 mm ²

Other connections

Connection method	Screw connection
Conductor cross section solid	0.14 mm ² ... 2.5 mm ²

Interfaces

Communication

Communication protocol	Modbus/TCP
	HTTP
	NTP
	DHCP
	FTP
Communication standard	IEEE 802.3
Connection method	RJ45
Transmission speed range	10 Mbps ... 100 Mbps

Dimensions

Width	72 mm
Height	90 mm
Depth	67 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP51 (Front)
Degree of protection	IP20 (Connections)
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 75 °C
Max. permissible relative humidity (operation)	80 %

Approval data

CE

Certificate	CE-compliant
-------------	--------------

MID

Identification	MID-compliant
----------------	---------------

Standards and regulations

Standards/specifications	EN 50470-1
	EN 50470-3

Mounting

Measuring instrument - EEM-EM377

2908590

<https://www.phoenixcontact.com/pc/products/2908590>



Mounting type	DIN rail mounting
Mounting position	Horizontal DIN rail

Measuring instrument - EEM-EM377


2908590

<https://www.phoenixcontact.com/pc/products/2908590>



Drawings

Connection diagram



Measuring instrument - EEM-EM377



2908590

<https://www.phoenixcontact.com/pc/products/2908590>

Approvals



EAC

Approval ID: RU *-DE.A*30.B.01628

MID

Approval ID: No. 308/MID

Measuring instrument - EEM-EM377



2908590

<https://www.phoenixcontact.com/pc/products/2908590>

Classifications

ECLASS

ECLASS-9.0	27142330
ECLASS-10.0.1	27142330
ECLASS-11.0	27142330

ETIM

ETIM 8.0	EC002301
----------	----------

UNSPSC

UNSPSC 21.0	41113600
-------------	----------

Measuring instrument - EEM-EM377



2908590

<https://www.phoenixcontact.com/pc/products/2908590>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2022 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com