

Coaxial PCB Connector 2x8A_82_MXPM-S50-0-1

Description

Straight PCB jack

Interface Standards

HUBER+SUHNER MXPM STD (Patent US 8,360,807 / Patent pend.)



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	70 GHz

Mechanical Data

Board mounting type	pin-in-hole / SMT
Weight	0.01 kg

Environmental Data

Operating temperature	0 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact		
Outer contact	Brass	SUCOPRO / Gold Plating
Body	Brass	SUCOPRO / Gold Plating

Related Documents

Outline drawing	DOU-00332824
Catalogue drawing	DCA-00364569

Ordering Information

Single package	2x8A_82_MXPM-S50-0-1/-11_NE
Tape and Reel package	2x8A_82_MXPM-S50-0-1/-11_NM

Remarks

Multicoax socket, 2x8 ganged, keyed

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[2x8A_82_MXPM-S50-0-1/-11_NE](#)