
Dimensions: [mm] Electrical Properties: Unit **Properties** Value Shielding Effectiveness @ 100 80 dΒ 10,0 ±0,8 dB Shielding Effectiveness @ 1 GHz 86 Surface Resistance 1) 0.08 Ω 1) Measurement equipment: Loresta AX MCP-T370 **General Information: Operating Temperature** -40 up to +85 °C (Scale-1:10) **Storage Conditions (in original** $< 40 \,^{\circ}\text{C}; < 75 \,^{\circ}\text{RH}$ packaging) **Moisture Sensitivity Level (MSL)** Flammability: UL94 V-0 (File Number E474708) Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Scale - 1:1 Material **Metallized Fiber** CHECKED REVISION DATE (YYYY-MM-DD) GENERAL TOLERANCE **Polyether Urethane Foam** ViMa 005.003 2020-03-06 DIN ISO 2768-1m Rayon Paper with acrylic adhesive **WE-LT Conductive Shielding** Reactive Polyurethane Hotmelt Würth Elektronik eiSos GmbH & Co. KG **Gasket** ORDER CODE EMC & Inductive Solutions Adhesive Max-Eyth-Str. 1 3021001 74638 Waldenburg Germany SIZE/TYPE STATUS Tel. +49 (0) 79 42 945 - 0 BUSINESS UNIT PAGE www.we-online.com eiSos Valid 1/3 Square eiSos@we-online.com



CHECKED REVISION DATE (YYYY-MM-DD) GENERAL TOLERANCE PROJECTION METHOD ViMa 005.003 2020-03-06 DIN ISO 2768-1m **WE-LT Conductive Shielding** Würth Elektronik eiSos GmbH & Co. KG Gasket ORDER CODE EMC & Inductive Solutions Max-Eyth-Str. 1 3021001 74638 Waldenburg SIZE/TYPE STATUS Tel. +49 (0) 79 42 945 - 0 www.we-online.com BUSINESS UNIT PAGE 2/3 eiSos Valid Square eiSos@we-online.com

Important Notes

The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

