

SK 5 - Shield connection clamp



3025338

<https://www.phoenixcontact.com/pc/products/3025338>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shield connection clamp, for shield on busbars, contact resistance < 1 mΩ

Your advantages

- Easy handling
- Spring-loaded, large-surface pressure plate
- Suitable for direct and busbar mounting
- Knurled screw
- As components, it is not possible to certify shield connections in accordance with the requirements of the directive and standards for electrical equipment in potentially explosive areas. As such, shield connection clamps can be used in the Ex area even without an appropriate approval or marking.

Commercial data

Item number	3025338
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BE7512
Catalog page	Page 568 (C-3-2019)
GTIN	4046356051835
Weight per piece (including packing)	13.9 g
Weight per piece (excluding packing)	13.42 g
Customs tariff number	85369010
Country of origin	CN

SK 5 - Shield connection clamp

3025338

<https://www.phoenixcontact.com/pc/products/3025338>



Technical data

Product properties

Product type	Shield connection clamp
Pitch	9 mm
Number of connections	1
Number of rows	1


Electrical properties

Maximum power dissipation for nominal condition	0 W
Contact resistance	< 0.001 Ω

Connection data

Grounding foot	Yes
Screw thread	M4
Tightening torque	... 0.4 Nm

Dimensions

Dimensional drawing	
Width	9 mm
Height	19.5 mm
Depth	46.8 mm
Pitch	9 mm

External dimensions

Outside diameter	2 mm ... 5 mm
------------------	---------------

Material specifications

Color	silver
Material	Steel

Cable/line

External cable diameter	2 mm ... 5 mm
-------------------------	---------------

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Mechanical tests

SK 5 - Shield connection clamp



3025338

<https://www.phoenixcontact.com/pc/products/3025338>

Mechanical strength

Result	Test passed
--------	-------------

Environmental and real-life conditions

Oscillation/broadband noise

Specification	DIN EN 50155 (VDE 0115-200):2008-03
Spectrum	Service life test category 1, class B, body mounted
Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$
ASD level	0.02g ² /Hz
Acceleration	0.8g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

Shocks

Specification	DIN EN 50155 (VDE 0115-200):2008-03
Pulse shape	Half-sine
Acceleration	5g
Shock duration	30 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Result	Test passed

Mounting

Mounting type	Neutral busbar
---------------	----------------

SK 5 - Shield connection clamp


3025338

<https://www.phoenixcontact.com/pc/products/3025338>



Drawings

Diagram




SK 5 - Shield connection clamp

3025338

<https://www.phoenixcontact.com/pc/products/3025338>



Dimensional drawing



SK 5 - Shield connection clamp



3025338

<https://www.phoenixcontact.com/pc/products/3025338>

Classifications

ECLASS

ECLASS-11.0	27141150
ECLASS-12.0	27141150
ECLASS-13.0	27250309

ETIM

ETIM 9.0	EC002020
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SK 5 - Shield connection clamp



3025338

<https://www.phoenixcontact.com/pc/products/3025338>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

SK 5 - Shield connection clamp

3025338

<https://www.phoenixcontact.com/pc/products/3025338>



Accessories

i Note: Applying some accessories below might limit this product.

NLS-CU 3/10 SN 1000MM - Neutral busbar

0402174

<https://www.phoenixcontact.com/pc/products/0402174>



Neutral busbar, DIN VDE 0611-4: 1991-02, material: Copper, tin-plated, color: silver

i Max. current carrying capacity: 140 A

AK 4 - Connection terminal block

0404017

<https://www.phoenixcontact.com/pc/products/0404017>



Connection terminal block, connection method: Screw connection, Rated cross section: 4 mm², cross section: 0.5 mm² - 6 mm², mounting: Neutral busbar, color: silver

SK 5 - Shield connection clamp

3025338

<https://www.phoenixcontact.com/pc/products/3025338>



AKG 4 GNYE - Connection terminal block

0421029

<https://www.phoenixcontact.com/pc/products/0421029>



Connection terminal block, nom. voltage: 300 V, nominal current: 41 A, connection method: Screw connection, Rated cross section: 4 mm², cross section: 0.5 mm² - 6 mm², mounting: Neutral busbar, color: green-yellow

AKG 4 BK - Connection terminal block

0421032

<https://www.phoenixcontact.com/pc/products/0421032>



Connection terminal block, nom. voltage: 300 V, nominal current: 41 A, connection method: Screw connection, Rated cross section: 4 mm², cross section: 0.5 mm² - 6 mm², mounting: Neutral busbar, color: black

SK 5 - Shield connection clamp

3025338

<https://www.phoenixcontact.com/pc/products/3025338>



AB-SK TOP - Support bracket

3062090

<https://www.phoenixcontact.com/pc/products/3062090>

Support bracket, Bracket for busbars, set every 20 cm, width: 5.2 mm, height: 102.4 mm, number of positions: 1, color: gray, mounting type: DIN rail mounting



AB-SK TOP INSULATED - Support bracket

3062074

<https://www.phoenixcontact.com/pc/products/3062074>

Support bracket, Bracket for busbars, set every 20 cm, width: 5.2 mm, height: 102.4 mm, number of positions: 2, color: gray, mounting type: DIN rail mounting



SK 5 - Shield connection clamp

3025338

<https://www.phoenixcontact.com/pc/products/3025338>



AB-SK - Support bracket

3025341

<https://www.phoenixcontact.com/pc/products/3025341>

Support bracket for busbars



AB-SK 65 - Support bracket

3026489

<https://www.phoenixcontact.com/pc/products/3026489>

Support bracket, Bracket for busbars, set every 20 cm, width: 6.2 mm, height: 95.5 mm, number of positions: 1, color: gray, mounting type: DIN rail mounting



SK 5 - Shield connection clamp

3025338

<https://www.phoenixcontact.com/pc/products/3025338>



AB-SKS 60 - Support bracket

3240223

<https://www.phoenixcontact.com/pc/products/3240223>

Support bracket for busbars




AB-SK-D TOP - Support bracket

3062100

<https://www.phoenixcontact.com/pc/products/3062100>

Support bracket, Bracket for busbars, set every 20 cm, width: 5.2 mm, height: 155.8 mm, number of positions: 2, color: gray, mounting type: DIN rail mounting



SK 5 - Shield connection clamp

3025338

<https://www.phoenixcontact.com/pc/products/3025338>



AB-SK-D TOP INSULATED - Support bracket

3062087

<https://www.phoenixcontact.com/pc/products/3062087>

Support bracket, Bracket for busbars, set every 20 cm, width: 5.2 mm, height: 155.8 mm, number of positions: 2, color: gray, mounting type: DIN rail mounting



AB-SK 65-D - Support bracket

3026900

<https://www.phoenixcontact.com/pc/products/3026900>

Support bracket, Bracket for busbars, set every 20 cm, width: 8.2 mm, height: 150 mm, number of positions: 2, color: gray, mounting type: DIN rail mounting



SK 5 - Shield connection clamp

3025338

<https://www.phoenixcontact.com/pc/products/3025338>



AB-SK 65-D INSULATED - Support bracket

3040889

<https://www.phoenixcontact.com/pc/products/3040889>

Support bracket, Bracket for busbars, set every 20 cm, width: 8.2 mm, height: 150 mm, number of positions: 2, color: gray, mounting type: DIN rail mounting



AB/SS - Support bracket

0404428

<https://www.phoenixcontact.com/pc/products/0404428>

Support bracket made from insulation material, with retaining screw, can be used with either 3 x 10 mm or 6 x 6 mm busbar, color: gray



SK 5 - Shield connection clamp

3025338

<https://www.phoenixcontact.com/pc/products/3025338>



AB/SS-M - Support bracket

3025888

<https://www.phoenixcontact.com/pc/products/3025888>




Support bracket made from insulation material, with retaining screw, can be used for 3 x 10 mm busbar, color: gray

AB/SKS - Support bracket

3240224

<https://www.phoenixcontact.com/pc/products/3240224>



Support bracket for busbars

SK 5 - Shield connection clamp

3025338

<https://www.phoenixcontact.com/pc/products/3025338>



AB-SK/E - Support bracket

3026476

<https://www.phoenixcontact.com/pc/products/3026476>

Support bracket, Bracket for busbars, set every 20 cm, depth: 20 mm, width: 56 mm, height: 10 mm, diameter: 4.5 mm, number of positions: 2, color: silver, mounting type: Direct mounting



AB-SK/E-NS 35 - Support bracket

3213111

<https://www.phoenixcontact.com/pc/products/3213111>

Support bracket, Bracket for busbars, set every 20 cm, depth: 33.7 mm, width: 56 mm, height: 50 mm, number of positions: 2, color: silver, mounting type: DIN rail mounting



Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com